



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HANNSBURG, PENNSYLVANIA, USA.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
-	-	0		RE-DRAWN WAS UTILUX 01.01192.01	-	-



REF. NOTE 2




Section A-A




Section B-B

NOTES:

- THIS PRODUCT IS UL APPROVED.
- 'UTILUX' OR 'AMP' LOGO STAMPED AS REQUIRED.
- WIRE RANGE
CONDUCTOR: 0.70mm² - 1.5mm²
INSULATION DIA: 2.4mm - 2.9mm



ELECTRO-TIN		BRASS		TAB QC 6.3 (H1192-ET)		1-1627025-2	
NATURAL		NICKEL SILVER		TAB QC 6.3 (H1192-B)		1-1627025-1	
NATURAL		BRASS		TAB QC 6.3 (H1192)		1-1627025-0	
FINISH		MATERIAL		DESCRIPTION (UTILUX P/N)		PART No.	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN: H.THAI 11.2.03		tyco Tyco Electronics Corporation Electronics AUSTRALIA TAB QC 6.3	
ALL DIMENSIONS IN mm:				CHK: W.RIEDE 11.2.03			
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD: P.TIMBRELL11.2.03			
DIMENSION (mm) TOLERANCE(±mm)				NAME:			
		LESS THAN 10 0.4		PRODUCT SPEC:		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
		OVER 10 TO 30 0.5		-			
		OVER 30 TO 80 0.7		APPLICATION SPEC:			
		OVER 80 TO 250 1.0		-			
ANGLES ±2°		WEIGHT: -		A3		C- 1627025	
MATERIAL REF. BLOCK		FINISH REF. BLOCK		CUSTOMER DRAWING		SCALE 5:1 SHEET 1 OF 1 REV 0	