




Automotive Parts > Automotive Connectors > Automotive Housings



Nominal Voltage Architecture: 12 V, 24 V, 48 V

Connector & Housing Type: Housing for Female Terminals

Number of Positions: 2

Sealable: Yes

Operating Temperature Range: -40 – 130 °C [-40 – 266 °F]

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Primary Locking Feature	Locking Lance
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	12 VDC
Nominal Voltage Architecture	12 V, 24 V, 48 V

Body Features



Cable Exit Angle	180 °
Primary Product Color	Black
Connector & Keying Code	A

Contact Features

Contact Size	1.2mm
Contact Type	Receptacle
Mating Tab Width	1.2 mm[.047 in]
Contact Current Rating (Max)	25 A

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA 66 GF30
Centerline (Pitch)	4 mm[.16 in]

Dimensions

Product Width	26.5 mm[1.04 in]
Product Length	15 mm[.59 in]
Connector Height	14.8 mm[.58 in]

Usage Conditions

Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]
Operating Temperature (Max)	130 °C[266 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

IP Rating	IPX4K, IPX9K
-----------	--------------

Packaging Features

Packaging Quantity	2000
Packaging Method	Box



Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-1703498-4
2POS, MCON 1.2 LL TAB SEALED
COD B



TE Part # 1-1703498-4
2POS, MCON 1.2 LL TAB SEALED
COD A



TE Part # CAT-M4595-T273
MCON Receptacle and Tab



TE Part # 2-2236952-5
2POS, MCON 1.2 LL TAB SEALED
COD B



TE Part # CAT-N14-RC4812
48V Ready 1.2mm Sealed Connectors

Also in the Series | MCON 1.2mm




Automotive Connector Caps & Covers (15)



Automotive Housings(354)



Automotive Seals & Cavity Plugs(16)




Automotive Terminals(90)

Customers Also Bought




TE Part #170140-1
187 FASTON, FLAG, REC., 16-20 AWG, BR



TE Part #368261-2
E-S MK-2(+) PLUG 2P ASSY



TE Part #776537-2
AS16, CAP ASSY, ST, 06P, E SEAL, CODE B




TE Part #967067-1
MQS SGL WIRE SEAL




TE Part #CAT-M8793-T273
MQS, RECEPTACLE AND TAB



TE Part #CAT-N13-MSLRTT12
MCON 1.2 Locking Lance Receptacle and Tab Terminals



TE Part #ZPF000000000015890
DTP 07-8-3A-K



TE Part #81568-000
VS-X1030-E SILVER PLATED TERMINAL

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_1-1670916-1_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1670916-1_E.2d_dxf.zip

English

1-1670916-1

12 V / 24 V / 48 V, 2 Position, Automotive Housing for Female Terminals, Wire-to-Wire, 4 mm [.16 in] Centerline, Sealable, Black, MCON 1.2mm



3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1670916-1_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English