



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **General Purpose Resistor**

Element Type: **Carbon Film, Thin Film**

Power Rating: **.25 W**

Resistance Class: **Up to 1kΩ**

Resistance Value: **12 Ω**

Features

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Carbon Film, Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	200 V
Power Rating	.25 W
Resistance Class	Up to 1kΩ
Resistance Value	12 Ω
Passive Component Tolerance	5 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	3.5 x 1.85 mm
------------------------------	---------------



Usage Conditions

Operating Temperature Range	-55 – 155 °C[-67 – 311 °F]
Temperature Coefficient	-1200 – 0 ppm/°C

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CFR16J12R

12 ohm, Carbon Film / Thin Film, General Purpose Resistor, 5 %, .25 W, -1200 – 0 ppm /°C, Axial-Leaded, Copper Termination, 3.5 x 1.85 mm, NEOHM CFR



TE Part # 1623930-3
CFR25 5% 10K



TE Part # 1623925-2
CFR100 5% 100R



TE Part # 1623932-8
CFR50 5% 10K



TE Part # 2-1623929-2
CFR200 5% 22K



TE Part # 1623927-8
CFR16 5% 120R

Also in the Series | NEOHM CFR



[Through-Hole Resistors\(378\)](#)

Customers Also Bought




TE Part #1-1623928-0
CFR16 5% 390K



TE Part #1-1623928-3
CFR16 5% 39R



TE Part #3-1623928-6
CFR16 5% 56R



TE Part #9-1879275-7
RP 2A 5K49 0.1% 15PPM CUT LENGTH



TE Part #4-1437561-7
TT11DGRA9T1/4="SW TOGGLE WITH



TE Part #4-2176086-4
3654 0402 51nH 5% 2K RL



TE Part #YACT24JA98SN000000
JAM NUT RECEPTACLE



TE Part #YACT26JD97SN000000
STRAIGHT PLUG

CFR16J12R

12 ohm, Carbon Film / Thin Film, General Purpose Resistor, 5 %, .25 W, -1200 – 0 ppm /°C, Axial-Leaded, Copper Termination, 3.5 x 1.85 mm, NEOHM CFR



Documents

Product Drawings

[CFR16 5% 12R](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1-1623927-0_BA.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-1623927-0_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1623927-0_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[Ceramic Film Fixed Resistors - Type CFR Series - Tyco Electronics Passives](#)

English