



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**
Element Type: **Metal Oxide Film**
Power Rating: **5 W**
Resistance Class: **Up to 1kΩ**
Resistance Value: **18 Ω**

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Metal Oxide Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	500 V
Power Rating	5 W
Resistance Class	Up to 1kΩ
Resistance Value	18 Ω
Passive Component Tolerance	5 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	25 x 8 mm
------------------------------	-----------



Usage Conditions

Operating Temperature Range	-55 – 235 °C[-67 – 455 °F]
Temperature Coefficient	±350 ppm/°C

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

ROX5SJ18R

18 ohm, Metal Oxide Film, Power Resistor, 5 %, 5 W, ±350 ppm/°C, Axial-Leaded, Copper Termination, 25 x 8 mm, Box, 2 Terminations, NEOHM ROX



TE Part # 1625881-2
1W STD M/OX 2% 220R



TE Part # 6-1676123-7
1/2W SM M/OX 5% 470R



TE Part # 2-1625892-1
3W SM M/OX 5% 1K0



TE Part # 4-1625886-1
1W SM M/OX 5% 820K




TE Part # 1625893-5
5W SM M/OX 5% 47K

Also in the Series | NEOHM ROX




[Through-Hole Resistors\(783\)](#)

Customers Also Bought




TE Part #3-84984-0
1mm FFC DIP V ASSY 30P TUBE



TE Part #5-146130-6
14 MODII HDR DRST SFMNT B/A LF



TE Part #7-1393238-2
RTD14110




TE Part #6-1614958-6
CPF 0805 4R64 0.1% 25ppm 1K RL




TE Part #1623929-6
CFR200 5% 120R



TE Part #1625893-4
5W SM M/OX 5% 22R



TE Part #8-2176243-5
CRGS0603 5% 10M



TE Part #1-2176379-4
RQ 0805 147R 0.1% 10PPM 5K RL



TE Part #3-2176412-7
5W XSM M/OX 5% 160R



TE Part #5-2176412-5
5W XSM M/OX 5% 910R

Documents

Product Drawings

5W SM M/OX 5% 18R

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1625893-5_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1625893-5_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1625893-5_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

Flame Proof Power Metal Oxide Film Resistors - Type ROX Series - Tyco Electronics Passives

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English