YR1B12R4CC ✔ ACTIVE

NEOHM | NEOHM R

TE Internal #: 1-1879026-0

12.4 ohm, Thin Film, Precision Resistor, .1 %, .25 W, ±15 ppm/°C, Axial-Leaded, Copper Termination, 6.3 x 2.3 mm, Ammo Packed, 2 Terminations, NEOHM R

View on TE.com >

Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Precision Resistor**

Element Type: **Thin Film**

Power Rating: **.25 W**

Resistance Class: **Up to 1kΩ**

Resistance Value: **12.4 Ω**

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film

Configuration Features

Number of Resistors	1

Electrical Characteristics

Operating Voltage	250 V
Power Rating	.25 W
Resistance Class	Up to 1kΩ
Resistance Value	12.4 Ω
Passive Component Tolerance	.1 %

Body Features

Lead Type	Axial-Leaded

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	6.3 x 2.3 mm

Usage Conditions

Operating Temperature Range	-65 – 155 °C[-85 – 311 °F]
Temperature Coefficient	±15 ppm/°C

Packaging Features

Packaging Method	Ammo Packed

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 2-1676913-7
YR1 0.1% 1M0



TE Part # 1622796-6
YR1 0.1% 10K



TE Part # 1622796-2
YR1 0.1% 100R




TE Part # 2-1676913-6
YR1 0.1% 1K0



TE Part # 1622796-1
YR1 0.1% 100K

Also in the Series | NEOHM R



Eurocard Connectors(1)



Through-Hole Resistors(484)


Customers Also Bought



TE Part #1SNG607010R0000
EP-LN-M25-LGR-A



TE Part #S8656XRRN
Panel,RHCP,fixed,rta,RNF 865-870MHz, 6dBi



TE Part #1-1123722-2
3.96 EP PLUG HSG 2P(NATURAL)




TE Part #2-1614892-3
CPF 0805 1K4 0.1% 25PPM 1K RL




TE Part #1624322-4
UPW25 0.1% 5PPM 10R




TE Part #1879026-7
YR1 0.1% 11R8



TE Part #9-1879663-0
H8 909R 0.1% 15PPM



TE Part #2-2176421-7
TLRP 2512 2.0W R050 1% 25PPM 4K RL



TE Part #2454985-2
ADE Next Gen, 2 Pos. SMT TU



TE Part #EM0605-000
D-436-0096-2

Documents

Product Drawings

YR1 0.1% 12R4

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1879026-0_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1879026-0_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1879026-0_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

Precision Metal Film Fixed Resistors - Type R Series

English