

HSA1018RJ

✓ ACTIVE

CGS | CGS HS

TE Internal #: 1-1625966-3


18 ohm, Wire Wound, 5 %, Power Resistor, 16 W, 2 Terminations,
±50 ppm/°C, Solder Lug, Loose Piece - Tray, 11 mm [.433 in]

Height, CGS HS

[View on TE.com >](#)



Passive Components > Resistors > Chassis Mount Resistors > Power Resistors: Aluminum Housed, HSA



Resistor Type: **Power Resistor**

Resistance Class: **Up to 1kΩ**

Resistance Value: **18 Ω**

Power Rating: **16 W**

Element Type: **Wire Wound**

[All Power Resistors: Aluminum Housed, HSA \(384\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	265 V
Resistance Class	Up to 1kΩ
Resistance Value	18 Ω
Power Rating	16 W
Passive Component Tolerance	5 %

Termination Features

Number of Terminations	2
------------------------	---



Chassis Mount Resistor Termination Type

Solder Lug

Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes
--------------------------	----------------------------

Dimensions

Product Height	11 mm[.433 in]
Product Length	36.5 mm[1.437 in]
Product Width	21 mm[.827 in]

Usage Conditions

Temperature Coefficient	±50 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Loose Piece - Tray
------------------	--------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts



TE Part # 1630027-1
HSC300 100R 5%



TE Part # CAT-C339-H85913
Power Resistors: Aluminum Housed, HSA



TE Part # 1625999-3
HSC100 10R 5%

Also in the Series | CGS HS



Automotive Housings(1)




Automotive Signal & Power Connector Housings(1)



Card Edge Connector Housings(1)



FFC Connectors(1)




High Speed Backplane Connectors(10)




RJ45 Connectors(1)

Customers Also Bought



TE Part #637411-000
MTCP-122-20P2



TE Part #435975-000
22759/43-22-6



TE Part #CAT-C7679-Z614
ZHD-CT LFH & Fluid Resistant Tube



TE Part #1-1609968-7
KEP 50A 1S HIGH PLUS SP WYE 440VAC



TE Part #2-1625966-8
HSA10 30R 5%



TE Part #8-1879212-2
CPF 0402 16R5 0.1% 25PPM 1K RL



TE Part #2-1879355-9
RR03 5% 62K AMMO



TE Part #1903611-5
0.50 SERIES CONN 12POS PLUG
HOUSING ASSY



TE Part #1939203-4
025 40P CAP HOUSING ASSY H-TYPE

Documents

Product Drawings

HSA10 18R 5%

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1625966-3_W.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1625966-3_W.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1625966-3_W.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

Aluminium Housed Power Resistors - Type HS Series

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English

HSA1018RJ

18 ohm, Wire Wound, 5 %, Power Resistor, 16 W, 2 Terminations, ±50 ppm/°C, Solder
Lug, Loose Piece - Tray, 11 mm [.433 in] Height, CGS HS

