CPF0603B4R99E ✔ ACTIVE


NEOHM | NEOHM CPF

TE Internal #: 1-1879217-5

4.99 ohm, Thin Film, Precision Resistor, .1 %, 0603, .063 W, ±25 ppm /°C, Solder, 2 Terminations, .45 mm [.018 in] Height, NEOHM CPF

View on TE.com >

Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Element Type: **Thin Film**

Package Size Code: **0603**

Power Rating: **.063 W**

Resistance Value: **4.99 Ω**

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0603

Configuration Features

Number of Resistors	1

Electrical Characteristics

Operating Voltage	50 V
Power Rating	.063 W
Resistance Value	4.99 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.45 mm[.018 in]
Product Length	1.55 mm[.061 in]
Product Width	.8 mm[.031 in]

Usage Conditions

Operating Temperature Range	-55 – 155 °C[-67 – 311 °F]
Temperature Coefficient	±25 ppm/°C

Industry Standards

Moisture Sensitivity Level	1

Packaging Features

Packaging Method	Tape & Reel

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts




TE Part # 4-1879217-6
CPF 0603 11R3 0.1% 25PPM 5K RL




TE Part # 1-1879217-9
CPF 0603 5R49 0.1% 25PPM 5K RL




TE Part # 8-1879217-8
CPF 0603 34R 0.1% 25PPM 5K RL



TE Part # 6-1879217-4
CPF 0603 18R2 0.1% 25PPM 5K RL




TE Part # 9-1879217-5
CPF 0603 40R2 0.1% 25PPM 5K RL



TE Part # 5-1879217-6
CPF 0603 14R7 0.1% 25PPM 5K RL

Also in the Series | NEOHM CPF



Surface Mount Resistors(5840)

Documents

Product Drawings

CPF 0603 4R99 0.1% 25PPM 5K RL

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1879217-5_BA.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1879217-5_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1879217-5_BA.3d_igs.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

CPF-1016

English