




FPC

TE Internal #: 1-1735042-2

1 mm [.039 in] Centerline, Non ZIF, Vertical, Surface Mount, Tin (Sn),
12 Position, FPC Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FPC Connectors



Centerline (Pitch): 1 mm [.039 in]

Insertion Force Type: **Non ZIF**

PCB Mount Orientation: **Vertical**

Termination Method to PCB: **Surface Mount**

Contact Mating Area Plating Material: **Tin (Sn)**

Features

Product Type Features

Connector & Contact Terminates To	Flexible Printed Circuit (FPC), Printed Circuit Board
Connector Product Type	Connector Assembly
Connector System	Flex-to-Board
PCB Connector Type	PCB Mount Receptacle
Insertion Force Type	Non ZIF

Configuration Features

Compatible With Wire & Cable Type	FFC, FPC
Number of Rows	1
PCB Mount Orientation	Vertical
Number of Positions	12

Electrical Characteristics

Operating Voltage	125 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	1 μm[39.37 μin]
Contact Current Rating (Max)	1 A



PCB Contact Termination Area Plating Material Thickness	1 μm[39.37 μin]
Contact Shape & Form	Single Beam
Contact Layout	Staggered Type A
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
Contact Type	Socket
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material	Tin (Sn)

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Mechanical Attachment

Connector Mounting Type	Board Mount
PCB Mount Retention	Without
Mating Alignment	With
PCB Mount Alignment	Without

Housing Features

Housing Material	Nylon GF
Centerline (Pitch)	1 mm[.039 in]

Dimensions

Accepts Flex Cable Thickness	.3 mm[.012 in]
Connector Width	4 mm[.157 in]
Connector Height	5.6 mm[.22 in]
Connector Length	14 mm[.551 in]

Usage Conditions

Operating Temperature Range	-20 – 85 °C[-4 – 185 °F]
-----------------------------	--------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Identification Marking

Circuit Identification Feature	With
--------------------------------	------

Packaging Features

Packaging Quantity	800
Packaging Method	Tape & Reel



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 245°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Customers Also Bought



TE Part #E776944001
VERSAFLEX-FR-1/8-09-SP



TE Part #32065
TERMINAL,BODY FLAG R 22-16 6




TE Part #1-87456-6
20 MODIV HSG DR MRKD .100CL



TE Part #3-794617-8
8P, MICRO MNL RCPT HSG, DBL ROW, GW V0




TE Part #1658527-2
622-0630LF FEM SOCKET,LEAD FREE




TE Part #2-1761608-1
IDC LOW PRO HDR 6P VERT SHT LA




TE Part #5-2213819-6
6X6 ILL TACT SMT 520GF COLD WHITE



TE Part #2438987-2
VERT USB3.2A(Shield Leg Solder)Au 15uM



TE Part #M3021-000005-2K5PG
PRESS XDCR M3021-000005-2K5PG



TE Part #M3031-000005-2K5PG
PRESS XDCR M3031-000005-2K5PG

Documents

Product Drawings
1MM FFC SMT V ASSY 12P EMBOSS

English

CAD Files

3D PDF

3D

Customer View Model
ENG_CVM_CVM_1-1735042-2_M.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1-1735042-2_M.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1-1735042-2_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



1-1773959-7-FPC-Connectors-CN

English

Product Specifications

Product Specification

English