




Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **General Purpose Resistor**

Element Type: **Thick Film**

Package Size Code: **0805**

Power Rating: **.5 W**

Resistance Value: **22 Ω**

Features

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Thick Film
Package Size Code	0805

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	150 V
Power Rating	.5 W
Resistance Value	22 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	5 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2



Dimensions

Product Height	.55 mm[.022 in]
Product Length	2 mm[.079 in]
Product Width	1.25 mm[.049 in]

Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CRGS0805J22R

22 ohm, Thick Film, General Purpose Resistor, 5 %, 0805, .5 W, ±100 ppm/°C, Solder, 2 Terminations, .55 mm [.022 in] Height, NEOHM CRGS



TE Part # 1-2176244-8
CRGS0805 5% 27R

TE Part # 1-2176244-6
CRGS0805 5% 18R

Also in the Series | NEOHM CRGS

Surface Mount Resistors(208)

Customers Also Bought

TE Part #CAT-HST-CGPT1
CGPT 2:1 Heat Shrink Tubing

TE Part #816555-SF
RN214-2.5-02-3M3

TE Part #0316676003
LSTT-R-3.2-0

TE Part #3-826949-2
32P MOD2 PIN HEADER

TE Part #6-1676915-7
YR1 0.1% 124K

TE Part #1-2176244-3
CRGS0805 5% 10R

TE Part #1-2176244-5
CRGS0805 5% 15R

TE Part #1-2176244-8
CRGS0805 5% 27R

TE Part #1478884-3
METRIC EMC GLAND M20X1.5



Documents

Product Drawings

CRGS0805 5% 22R

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2176244-7_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2176244-7_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2176244-7_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD Anti-Surge Thick Film Chip Resistor - Type CRGS Series - Tyco Electronics Passives

English