

RP73D2A348KBD

✓ ACTIVE

Holsworthy | Holsworthy RP73


TE Internal #: 1-1879281-8

348K ohm, Thin Film, Precision Resistor, .1 %, 0805, .125 W, ±15 ppm/°C, Solder, 2 Terminations, .55 mm [.022 in] Height, Holsworthy RP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**
Element Type: **Thin Film**
Package Size Code: **0805**
Power Rating: **.125 W**
Resistance Value: **348K Ω**

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0805

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	150 V
Power Rating	.125 W
Resistance Value	348K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	2 mm[.079 in]
Product Width	1.25 mm[.049 in]



Usage Conditions

Temperature Coefficient	±15 ppm/°C
-------------------------	------------

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

RP73D2A348KBTD


348K ohm, Thin Film, Precision Resistor, .1 %, 0805, .125 W, ±15 ppm/°C, Solder, 2 Terminations, .55 mm [.022 in] Height, Holsworthy RP73




TE Part # 2-1879279-6
RP 2A 75K 0.1% 15PPM 1K RL




TE Part # 5-1879743-7
RP 1J 18R2 0.1% 15PPM CUT LENGTH



TE Part # 2-1879747-4
RP 1J 110K 0.1% 15PPM CUT LENGTH



TE Part # 5-1879267-0
RP 2B 1M0 0.1% 15PPM 1K RL



TE Part # 9-1879252-4
RP 2B 10R 0.1% 15PPM CUT LENGTH

Also in the Series | [Holsworthy RP73](#)



[Surface Mount Resistors\(4227\)](#)

Customers Also Bought



TE Part #1-830611-0
LGH 1/2 SNGL MLD END




TE Part #9-1625971-5
HSA25 R01 10%



TE Part #1-1879353-9
RR02 5% 24K AMMO



TE Part #7-1879354-5
RR03 5% 390R AMMO




TE Part #7-1879648-1
H4P 287R 0.5% 100PPM



TE Part #7-2176305-3
RP 1E 0.1W 604R 0.1% 25PPM 5K RL




TE Part #3-2176307-2
RP 1E 0.1W 26K1 0.1% 25PPM 5K RL




TE Part #2337238-3
TACT MINI GW 5.2X5.2X2 160GF





TE Part #3-1437162-8
[FSP-12A-11](#)



TE Part #2-2176392-9
[RQ 1206 261K 0.1% 10PPM 5K RL](#)

Documents

Product Drawings

[RP 2A 348K 0.1% 15PPM 5K RL](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-1879281-8_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1879281-8_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1879281-8_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[RP73-0915](#)

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English