




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.51 – 1.31 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.51 mm [.02 in]**

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

--



	.095 in
Wire Insulation Support	Without
Mating Retention Type	Double Lock Plate

Dimensions

Product Length	28.11 mm[1.107 in]
Terminal Material Thickness	.51 mm[.02 in]
Wire Size	.51 – 1.31 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Packaging Features

Packaging Quantity	2500
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 62384-1 110 FASTON TAB 22-18 AWG TPBR	 TE Part # 42490-4 187 FASTON TAB 22-18 AWG BR	 TE Part # 63919-1 187 FASTON TAB 18-14 AWG TPBR	 TE Part # 1217118-1 110 FASTON,TAB,20-16 AWG,PTBR
 TE Part # 62531-1 205 FASTON TAB 18-14 AWG TPBR	 TE Part # 62887-1 110 FASTON,TAB,20-16 AWG,TPBR	 TE Part # 60850-2 187 FASTON TAB 18-14 AWG TPBR	 TE Part # 60850-1 187 FASTON TAB 18-14 AWG BR
 TE Part # 42490-3 187 FASTON TAB 22-18 AWG TPBR			


Also in the Series | FASTON 187

 Crimp Terminal Housings(40)	 Insertion & Extraction Tools(1)	 Insulation Boots & Sleeves(1)	 PCB Terminals(42)
---------------------------------	-------------------------------------	-----------------------------------	-----------------------




[Quick Disconnects\(197\)](#)


Customers Also Bought




TE Part #CC2644-000
[B-106-8502CS100](#)




TE Part #CC2628-000
[B-106-3631CS100](#)




TE Part #CC2637-000
[B-106-1802CS100](#)




TE Part #CC2631-000
[B-106-7401CS100](#)




TE Part #CC2643-000
[B-106-7502CS100](#)




TE Part #CC2649-000
[B-106-1803CS50](#)




TE Part #CC2621-000
[B-106-1501CS100](#)



TE Part #CC2641-000
[B-106-3632CS100](#)



TE Part #CC2645-000
[D-406-0003CS50](#)



TE Part #CC2630-000
[B-106-4631CS100](#)

Documents

[Product Drawings](#)
[187 FASTON,TAB,TPBR](#)

English

[CAD Files](#)
[3D PDF](#)

3D

[Customer View Model](#)
[ENG_CVM_CVM_1217891-1_C.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_1217891-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1217891-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON TERMINALS \(INSULATED AND UNINSULATED\) - FULL CATALOG](#)

English

Agency Approvals

[UL Report](#)

English