1-2236898-5 ✔ ACTIVE

MCON | MCON 1.2mm


TE Internal #: 1-2236898-5

12 V / 24 V / 48 V, 5 Position, Automotive Housing for Female Terminals, Wire-to-Wire, 4 mm [.16 in] Centerline, Sealable, Black, MCON 1.2mm

View on TE.com >

Automotive Parts > Automotive Connectors > Automotive Housings




Nominal Voltage Architecture: **12 V, 24 V, 48 V**

Connector & Housing Type: **Housing for Female Terminals**

Number of Positions: **5**

Sealable: **Yes**

Operating Temperature Range: **-40 – 130 °C [-40 – 266 °F]**

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Primary Locking Feature	Locking Lance
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	5
Number of Rows	1

Electrical Characteristics

Nominal Voltage Architecture	12 V, 24 V, 48 V

Body Features

Cable Exit Angle	180 °

Primary Product Color	Black
Connector & Keying Code	A

Contact Features

Contact Size	1.2mm
Contact Type	Receptacle
Mating Tab Width	1.2 mm[.047 in]
Contact Current Rating (Max)	15 A

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	Yes
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA 66 GF30
Centerline (Pitch)	4 mm[.16 in]

Dimensions

Product Width	26.5 mm[1.043 in]
Product Length	28.7 mm[1.13 in]
Connector Height	16.5 mm[.65 in]

Usage Conditions

Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]
Operating Temperature (Max)	130 °C[266 °F]

Operation/Application

Circuit Application	Power

Industry Standards

IP Rating	IPX9K

Packaging Features

Packaging Method	Box
Packaging Quantity	1000

Other

Serviceable	Yes
Connector Position Assurance Capable	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Dodecamethylcyclohexasiloxane (D6) (.5% in 27519454043) Decamethylcyclopentasiloxane (D5) (.5% in 27519454043) Octamethylcyclotetrasiloxane (D4) (.5% in 27519454043) **Article Safe Usage Statements:** Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1-2236954-5
5POS, MCON 1.2 LL TAB SEALED COD A



TE Part # 967067-1
MQS SGL WIRE SEAL



TE Part # 5-1579007-3
EXTRACTION TOOL



TE Part # 967067-2
MQS EINZELLEITDICHT



TE Part # CAT-N13-MSLRTT12
MCON 1.2 Locking Lance Receptacle and Tab Terminals




TE Part # CAT-N13-MSLLT12
MCON 1.2 48V Locking Lance Receptacle and Tab Terminals




TE Part # 963142-2
SWS,MQS,CVTY DIA,4.0,GRY

Also in the Series | MCON 1.2mm



Automotive Connector Locks & Position Assurance(9)




Automotive Housings(352)



Automotive Seals & Cavity Plugs(16)



Automotive Signal & Power Connector Housings(348)



Other Automotive Connector Accessories(12)


Customers Also Bought



TE Part #0528-002-6005
BKSHL, 60P, BLK, PLG, RA, NW 17



TE Part #DRC26-60S07
PLG, 60P, BLK, N, 07



TE Part #142685-3
L.I.F PL CONTACT 5MM 0.35-1 MM2 PTPPHBZ




TE Part #1452598-1
2 POS. GET FEMALE ASSY



TE Part #3-2209520-3
46POS,MCON 1.2,REC HSG ASSY,SLD



TE Part #2219501-2
4POS,060,PLUG ASSY



TE Part #2300007-1
24POS,0.64 MALE GEN. Y,PIN HSG, ASSY



TE Part #CAT-J58-NCP
NTSEAL Cavity Plugs



TE Part #1703727-1
2POS,JPT,HOUSING,ASSY,BK

Documents

Product Drawings

5POS, MCON 1.2 LL REC SEALED

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2236898-5_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2236898-5_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2236898-5_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English