




Automotive Parts > Automotive Cable Assemblies > Electric, Hybrid & Fuel Cell Cable Assemblies



Operating Voltage: 850 VDC

Cable Assembly Configuration: Single Ended

Cable Assembly Length: 3 m [9.84 ft]

Cable Assembly (End A): HVP800 Receptacle

Operating Temperature Range: -40 – 140 °C [-40 – 284 °F]

Features

Product Type Features

Sealable	Yes
Cable Assembly (End A)	HVP800 Receptacle

Electrical Characteristics

Operating Voltage	850 VDC
-------------------	---------

Usage Conditions

Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	Yes
----------	-----

Other

Cable Assembly Configuration	Single Ended
Cable Assembly Length	3 m[9.84 ft]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2208243-1 CPA,HVP 800	 TE Part # 2141212-1 8MM HV,SOCKET PIN TERMINAL	 TE Part # 9-2141157-2 SHIELD CRIMP FERRULE,90DEG	 TE Part # 2141159-1 FINGER PROT CAP 8MM HV,90DEG
 TE Part # 9-2141158-2 CU ALLOY,SHIELD,8MM HV,CONN HSG,90 DEG	 TE Part # 2141153-1 LEVER,2POS,90DEG	 TE Part # 2141155-2 PROTEC. COVER 8MM HV,90DEG	 TE Part # 2141227-1 2POS,PIN DIA 8.0,PIN HSG,ASSY,SLD



Also in the Series | AMP+ HVP800



Customers Also Bought



Documents

Product Drawings
2POS,HVP800,90 DEG,35 SQMM,COD A

English

CAD Files
3D PDF

3D



Customer View Model

[ENG_CVM_CVM_1-2286946-3_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2286946-3_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2286946-3_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English