




Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Current Sensing Resistor**

Element Type: **Metal Strip**

Package Size Code: **1206**

Power Rating: **1 W**

Resistance Value: **.01 Ω**

Features

Product Type Features

Resistor Type	Current Sensing Resistor
Element Type	Metal Strip
Package Size Code	1206

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	1 W
Resistance Value	.01 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions





Product Height	.55 mm[.022 in]
Product Length	3.15 mm[.124 in]
Product Width	1.45 mm[.057 in]

Usage Conditions

Temperature Coefficient	±75 ppm/°C
-------------------------	------------

Industry Standards

ESD HBM Classification	2
UL Flammability Rating	UL 94V-0
Industry Standard	AEC-Q200 Compliant
Moisture Sensitivity Level	1

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-2176467-5
TLRP 1206 1.0W R012 1% 75PPM 5K RL

TE Part # 1-2176467-3
TLRP 1206 1.0W R008 1% 75PPM 5K RL

Also in the Series | CGS TLRP

Surface Mount Resistors(239)

Customers Also Bought

TE Part #204763-E
SMCB 26 F AB VV 7-23 CL * H007 137 E002

TE Part #2-487406-6
RCPT CONTACT,STD PRESS,FFC

TE Part #2007135-1
SFP+ 1x4 CageAssembly w/ EMI gasket

TE Part #2007722-1
IMP100S,R,RA4P16C,RG,39

TE Part #2176467-9
TLRP 1206 1.0W R003 1% 75PPM 5K RL

TE Part #1-2176467-1
TLRP 1206 1.0W R005 1% 75PPM 5K RL

TE Part #1-2176467-6
TLRP 1206 1.0W R015 1% 75PPM 5K RL

TE Part #2-2176467-2
TLRP 1206 1.0W R003 1% 100PPM 5K RL



Documents

CAD Files

Customer View Model

ENG_CVM_CVM_1-2176467-4_BA1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1-2176467-4_BA1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2176467-4_BA1.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD Low Ohmic Current Sense Resistors - Type TLRP Series

English