



TE Internal #: 1-2213396-1  
 3 Position Circular Connector, Cable-to-Cable, A Code, 0 Power  
 Positions, 0 Signal Positions

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Cable**

Number of Positions: **3**

Polarization Code: **A**

Number of Power Positions: **0**

Number of Signal Positions: **0**

### Features

#### Product Type Features

Prewired	No
Connector System	Cable-to-Cable

#### Configuration Features

Keying & Polarized Position Locations	Normal
Number of Positions	3
Number of Power Positions	0
Number of Signal Positions	0

#### Body Features

Primary Product Color	Black
-----------------------	-------

#### Mechanical Attachment

Polarization Code	A
-------------------	---

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Customers Also Bought



## Documents

### Product Drawings

#### NECTOR M CONTACTS POSITIONER

English

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-2213396-1\\_B.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-2213396-1\\_B.3d\\_stp.zip](#)

English

1-2213396-1

3 Position Circular Connector, Cable-to-Cable, A Code, 0 Power Positions, 0 Signal Positions



### Customer View Model

[ENG\\_CVM\\_CVM\\_1-2213396-1\\_B.2d\\_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.