



Connectors > Lighting Connectors > Street Lighting Controls > Street Lighting Accessories



Lighting Product Type: **Cover**

Primary Product Color: **Yellow**

Product Diameter: **81 mm [3.12 in]**

Features

Product Type Features

Lighting Product Type	Cover
-----------------------	-------

Body Features

Primary Product Color	Yellow
-----------------------	--------

Dimensions

Product Diameter	81 mm[3.12 in]
------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2024 (240)
 Candidate List Declared Against: JAN 2024 (240)
 SVHC > Threshold:
 UV-329 (.5% in Component Part)

Article Safe Usage Statements:
 Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by



following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-ST833-P5663A
Photo Control Base



TE Part # 1-2306130-1
COVER, LIGHT CONTROLLER, 81MM DIA., MED




TE Part # 1-2336396-2
ASSEMBLY, LIGHT CONTROLLER BASE, W/VENT




TE Part # 2336396-2
ASSEMBLY, LIGHT CONTROLLER BASE, W/VENT


Also in the Series | LUMAWISE Endurance N




Street Lighting Accessories(18)




Street Lighting Base Assemblies(19)



Street Lighting Open & Shorting Caps (3)




Street Lighting Power Management(6)



Street Lighting Receptacles(25)

Customers Also Bought

TE Part #1-770174-0
04P MINI-UMNL ASSY V0 SNNI*TE Part #1-2213730-1
LIGHT CONTROL BASE ASSY76MM 7
POSITIONTE Part #2213871-3
LIGHT CONTROLLER BASE ASSY,
81MM DIA, 7POS

Documents

Product Drawings

[COVER, LIGHT CONTROLLER, 81MM DIA., MED](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-2306130-2_C2.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2306130-2_C2.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2306130-2_C2.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL_CERT_CB_US_37285_C1](#)

English

1-2306130-2

Street Lighting Accessories, Cover, Yellow, Diameter 81 mm [3.12 in], LUMAWISE
Endurance N

