



Standard Timer

TE Internal #: 1-2315717-2

2 Position, Plug, Housing, Crimp, Wire-to-Board, UL 94V-0, 5 mm [.197 in] Centerline, 1 Row, Wire & Cable, Power & Signal, Standard Timer

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**

Connector & Housing Type: **Plug**

Mating Retention Type: **Latch**

Connector System: **Wire-to-Board**

UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Rows	1

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Current Rating (Max)	16 A
------------------------------	------

Termination Features

--	--



Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Locking Latch Between Cavity Number	1&2
-------------------------------------	-----

Panel Mount Feature	Without
---------------------	---------

Mating Retention Type	Latch
-----------------------	-------

Mating Retention	With
------------------	------

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	5 mm [.197 in]
--------------------	----------------

Housing Material	PA 66
------------------	-------

Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Glow Wire Rating	Glow Wire
------------------	-----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
--	---
















Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 964201-4 STD TIMER CONTACT</p>	 <p>TE Part # 964203-1 STD PW TIMER CONTACT</p>	 <p>TE Part # 964203-2 STD PW TIMER CONTACT</p>	 <p>TE Part # 964203-3 STD PW TIMER CONTACT</p>
 <p>TE Part # 964204-1 STD-POW-TIM KONTAKT</p>	 <p>TE Part # 964201-3 STD TIMER CONTACT</p>	 <p>TE Part # 6-1971845-2 2P, RAST 5 Tab Header, THV</p>	 <p>TE Part # 964203-4 STD PW TIMER CONTACT</p>
 <p>TE Part # 1241961-3 STD TIM HOUSING MKII 2POS</p>	 <p>TE Part # 964203-5 STD PW TIMER CONTACT</p>	 <p>TE Part # 964201-1 STD TIMER CONTACT</p>	 <p>TE Part # 964204-3 STD-POW-TIM KONTAKT</p>
 <p>TE Part # 964204-5 STD-POW-TIM KONTAKT</p>	 <p>TE Part # 964201-2 STD TIMER CONTACT</p>	 <p>TE Part # 964202-1 STD TIMER CONTACT</p>	


Also in the Series | Standard Timer



Automotive Terminals(6)




Connector Contacts(2)



Rectangular Connector Housings(11)



Rectangular Power Connectors(4)



Standard Edge Connectors(11)



Wire-to-Board Connector Assemblies
& Housings(11)


Customers Also Bought



TE Part #63933-2
250 PL MKIII REC. 22-18AWG TPBR



TE Part #521204-6
RAST 5,HSG,2P,POSILOCK MKIII



TE Part #521766-1
250 HSG. PL MKIII REC. 10mm 2P NAT



TE Part #1744144-1
EP-II CONTACT LANCELESS, 22-18



TE Part #1969442-6
EP 2.5 TPA Housing, 6 Pos



TE Part #1969443-6
EP 2.5 TPA Retainer, 6 Pos



TE Part #2132781-6
06P EP-II HOUSING, NATURAL

Documents

Product Drawings

[STD TIMER PLUG HSG 2P MKII](#)

English

CAD Files

[3D PDF](#)

[3D](#)



Customer View Model

[ENG_CVM_CVM_1-2315717-2_E.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2315717-2_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2315717-2_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[RAST Connector System Catalog](#)

English

Product Specifications

[Product Specification](#)

English

Agency Approvals

[VDE Certificate](#)

English