



Terminals & Splices > Foil Terminals



Accepts Foil Thickness (Max): **.4 mm [.016 in]**

Terminal Plating Material: **Tin**

Packaging Method: **Box**

Features

Contact Features

Terminal Plating Material	Tin
---------------------------	-----

Termination Features

Accepts Foil Thickness (Max)	.4 mm[.016 in]
------------------------------	----------------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Quantity	500
Packaging Method	Box

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250)



Candidate List Declared Against: JUNE 2025 (250)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



REPRESENTATION ONLY

TE Part # 68026
DAHT TERMI-FOIL ASSY

Also in the Series | TERMI-FOIL



Foil Terminals(23)


Customers Also Bought



TE Part #603891J001
V4-1.0-0-SP-SM



TE Part #62887-1
110 FASTON,TAB,20-16 AWG,TPBR



TE Part #7-520366-2
ULTRAFast 110 ASSY REC 26-22
TPBR LP



TE Part #1393249-7
W58-XB1A4A-10=W58



TE Part #1-1423696-6
BOOTSEAL,M11,CLEAR,SILICONE



TE Part #1513472-1
UAM Assembly



TE Part #6609056-3
10MV1=F7758 S0



TE Part #CAT-C8114-P2
CORCOM P SERIES MULTI-
FUNCTION INLET FIL



TE Part #1624364-2
NTC0805 5% 4K7

Documents

CAD Files

Customer View Model

[ENG_CVM_1-332006-0_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-332006-0_C.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-332006-0_C.2d_dxf.zip](#)

English

3D PDF

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-332006-0_H.2d_dxf.zip](#)

English

Customer View Model



[ENG_CVM_CVM_1-332006-0_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-332006-0_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.