




TE Internal #: 136311-2  
 Rings & Spades, Splice, 6AWG Wire Size, 13.3mm<sup>2</sup> Wire Size,  
 26240CMA Wire Size, Closed Barrel, Straight, Barrel Inside  
 Diameter .23 in [5.9 mm]

[View on TE.com >](#)

Terminals & Splices > Rings & Spades



Terminal & Splice Type: **Splice**

Wire Size: **26240 CMA**

Ring & Spade Barrel Type: **Closed Barrel**

## Features

### Product Type Features

Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

### Configuration Features

Number of Holes	1
Terminal Angle	Straight

### Body Features

Ring & Spade Plating Material	Nickel
-------------------------------	--------

### Contact Features

Contact Base Material	Copper (Cu)
Terminal & Splice Type	Splice
Ring & Spade Terminal Orientation	Straight
Underplating Material	None

## Dimensions



Wire Size	26240 CMA
Barrel Inside Diameter	5.9 mm[.23 in]

### Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	343 °C[649 °F]

### Operation/Application

Heavy Duty	No
------------	----

### Packaging Features

Packaging Quantity	500
Ring & Spade Packaging Method	Box

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1490414-2  
HYP10 SOLIS HD 6-4AWG INDENTER



TE Part # 1490413-2  
HYP10 SOLIS HD 8AWG NEST



TE Part # 48127  
HYP8 SOLIS 6-2AWG INDENTER



TE Part # 48128  
HYP8 SOLIS 6AWG NEST



TE Part # 69217  
HYP8/10 SOLIS 6AWG DIE SET



TE Part # 68136  
PNEU HT SOLIS 6 ASSY

## Customers Also Bought



TE Part #132076-1  
STRATOTHERM 1/0 NIPL



TE Part #1577647-1  
TERMINAL RT PIDG PEEK STRATO 10 AWG



TE Part #323754  
SPLICE,SOLIS PARA HR 12-10



TE Part #323794  
SPLICE,SOLIS PARA HR 16-14



TE Part #557952-000  
MTC100-KT2-0079



TE Part #ZPF000000000017864  
FAST-E 01 F-X-A 00 B



TE Part #1577632-1  
TERMINAL RT PIDG PEEK STRATO 18-16 AWG



TE Part #150453  
TERM,RING,SOLIS,STRAT,2 AWG, 5 /16,NI



TE Part #449233-000  
208M714-19B10



TE Part #201518-000  
208M718-19B12



## Documents

### Product Drawings

#### TERMINAL SOLISTRAND STRATOTHERM

English

---

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_136311-2\\_A.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_136311-2\\_A.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_136311-2\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Environmental Compliance

#### TE Material Declaration

English