1473288-1 ✔ ACTIVE

AMP | Micro Timer II

TE Internal #: 1473288-1

6 Position, Gray, Locking Device, PA 66, -40 – 85 °C [-40 – 185 °F], Micro Timer II

View on TE.com >

Automotive Parts > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance



Number of Positions: **6**

Primary Product Color: **Gray**

Connector & Contact Retention Accessory Type: **Locking Device**

Primary Product Material: **PA 66**

Operating Temperature Range: **-40 – 85 °C [-40 – 185 °F]**

Features

Product Type Features

Sealable	No
Connector & Contact Retention Accessory Type	Locking Device

Configuration Features

Number of Positions	6

Body Features

Primary Product Color	Gray
Primary Product Material	PA 66

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]

Industry Standards

UL Flammability Rating	UL 94HB

Packaging Features

Packaging Method	Bag
Packaging Quantity	1200

Other

Serviceable	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 936784-2
CLIP FOR MT-II/JPT SLD 20P/36P



TE Part # 1473284-1
MICRO TIMER II 6POS PLUG ASSY

Also in the Series | Micro Timer II



Automotive Connector Locks & Position Assurance(1)



Automotive Housings(40)



Automotive Seals & Cavity Plugs(1)




Automotive Signal & Power Connector Housings(40)


Customers Also Bought



TE Part #CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part #936059-1
2.8MM SLD 2P PLUG ASSY



TE Part #936059-2
2.8MM SLD 2P PLUG ASSY



TE Part #1-1355134-1
RETAINER 94P



TE Part #2005372-2
MT-II SLD 6P PLUG ASSY(A) BLK



TE Part #2005390-6
JPT SLD 3P PLUG ASSY-1S BLK



TE Part #2109258-4
MCON 1.2 CAVITY PLUG FOR 0.75MM



TE Part #3-2005475-2
PCU SLD 105P PLUG ASSY(B-RH)

Documents

Product Drawings

MICRO TIMER II 6POS SECONDARY

English

CAD Files

Customer View Model

ENG_CVM_1473288-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_1473288-1_A.3d_stp.zip

English

Customer View Model

ENG_CVM_1473288-1_A.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English