



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 203191-E
 MJIM IM 1X1 S 88 * X R THRU * L1A M3D01



TE Part # 203501-E
 MJIM IMV 1X1 * * * * * THRU * * H3D02 *



TE Part # 203412-E
 MJIM IMV 1X1 S 88 * X R THRU * L1 H3D01




TE Part # 203336-E
 MJIM IM 1X1 S 88 GF5 X R THRU * L1A H3D0



TE Part # 133919-E
MJ HS G5 * 8 8 4B * GF5 T * 30 * J 3
133



TE Part # 203543-E
MJ HS VG * 8 8 4 *** 999999 30 3/4 J
3



TE Part # 133421-E
MJ CS ** 8 8 * ** * 30 * J 3 133942



TE Part # 133934-E
MJ HS V5 * 8 8 * ** * 50 * J 3 133819



TE Part # 203354-E
MJIM IMR 1X1 S 88 GF5 X R THRU *
L1A M3D



TE Part # 133611-E
MJ LSS ** 8 8 * ** STP * 30 * J 3 2034



TE Part # 133208-E
MJ HS G * 8 8 2B * GF5 ** 30 3/4 J 3
13



TE Part # 203306-E
MJIM IM 1X2 S 810 GF5 * R THRU *
L1A M5B



TE Part # 203199-E
MJIM IM 1X1 S 88 GF5 X R THRU *
L2A M3D0




TE Part # 203344-E
MJIM IMV 1X1 S 810 * X R THRU * L3A
M5B0



TE Part # 203301-E
MJIM IM 1X4 S 810 GF5 T R THRU *
L1A M5B



TE Part # 203215-E
MJIM IM 1X1 S 810 GF5 X R THRU *
L9A M5B



TE Part # 133080-E
MJ DS-LG5 ** 8 8 16 * GF9 T * 30 * J 3



TE Part # 203492-E
MJ HS G5 * 8 8 2A * GF5 ** 50 * J 3
203



TE Part # 203355-E
MJIM IMR 1X1 S 88 GF5 X R THRU *
L2A M3D



TE Part # 203342-E
MJIM IMV 1X1 S 810 * X R THRU * L1A
M5B0

Customers Also Bought



TE Part #42806-2
250 FASTON REC 18-14 AWG TPBR



TE Part #170048-2
110 FASTON,REC.,24-20 AWG,TPBR



TE Part #1-175217-3
DYNAMIC D-3 REC CONT. M AU 0.76
L/P



TE Part #CAT-D9934-A75E
Header Assembly: Wire-to-Board, 15A,
gold or tin plated



Documents

Product Drawings

[DUST CAP](#)

Japanese

CAD Files

Customer View Model

[ENG_CVM_CVM_1554260-1_A.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1554260-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1554260-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English