


1-583990-3 x OBSOLETE

TE Internal #: 1-583990-3

TE Internal Description: AMP LF CONT STRIP

[View on TE.com >](#)



Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #163618-1
CIS COSI PIN POST



TE Part #6-216792-4
AMP LATCH ASSY




TE Part #964976-6
MODU2MM BU-GEH 2X6P



TE Part #964976-7
MODU2MM BU-GEH 2X7P



TE Part #969047-3
MODU CRIMP CONTACT



TE Part #6-216791-0
AMP LATCH D/P ASSY



TE Part #5750340-1
Mini DIN, 8 pos, Vertical, Shield



TE Part #1991231-2
EMC CRIMP SLEEVE. IPT 16-50mms



TE Part #1991234-1
SHIELD BODY & WAVE SPRING ASSY

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-583990-3_AA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-583990-3_AA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-583990-3_AA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

Japanese



AMP-LEAF Contact

English

Application Specification

Japanese

AMP-LEAF Contacts

Japanese

Instruction Sheets

Instruction Sheet (U.S.)

English

Hand Crimping Tool 90028-3

English

Agency Approvals

Agency Approval Document

English