

1612281-1 ✓ ACTIVE

AMP | 0.64/025 Connector System


TE Internal #: 1612281-1

Gray, PBT, Lever, -40 – 140 °C [-40 – 284 °F], 0.64/025 Connector System

[View on TE.com >](#)



Automotive Parts > Automotive Connector Accessories > Other Automotive Connector Accessories



Primary Product Color: **Gray**

Primary Product Material: **PBT**

Automotive Connector Accessory Type: **Lever**

Operating Temperature Range: **-40 – 140 °C [-40 – 284 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Lever
-------------------------------------	-------

Body Features

Primary Product Color	Gray
Primary Product Material	PBT

Usage Conditions

Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Bag
Packaging Quantity	40

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025
(247)

Candidate List Declared Against: JAN 2025
(247)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | 0.64/025 Connector System






Automotive Terminals(17)


Customers Also Bought



TE Part #368388-1
MOS RETAINER HSG FOR 40P




TE Part #936054-1
CAVITY PLUG(ECU 40P&81P ASSY)



TE Part #1473252-1
40POS MIXED MOS REC SEALED




TE Part #1473255-1
MOS 40P LEVER(L) ASSY



TE Part #1670144-3
MCON 1.2 CB REC SRC AG



TE Part #2013360-2
0.50/1.0 SEALED WIRE COVER 140POS




TE Part #2069401-1
0.5 SEALED RECEPTACLE CONTACT
Au



TE Part #2272976-3
Right Angle Wire Dress



TE Part #2375551-1
Wire Cover Mcon1.2 Connector 6Pos.



TE Part #2287717-1
REC CONN CVR,130POS,HYBRID,
90DEG,III

Documents

Product Drawings

[SEALED 0.64/2.3II 126POS LEVER](#)

Japanese

CAD Files

Customer View Model

[ENG_CVM_CVM_1612281-1_K.2d_dxf.zip](#)

English

[3D PDF](#)



3D

Customer View Model

[ENG_CVM_CVM_1612281-1_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1612281-1_K.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

CRIMPING OF SEALED 0.64 RECEPTACLE

Japanese

[Application Specification](#)

Japanese

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

[Instruction Sheet \(non U.S.\)](#)

Japanese