



Passive Components > Inductors > High Frequency & RF Inductors



Inductor Type: **High Frequency**
Package Size Code: **0603**
Inductance: **.039 μ H**
Current Rating (Max): **600 mA**
DC Resistance: **.25 Ω**

Features

Product Type Features

Inductor Type	High Frequency
Package Size Code	0603
Element Type	Wire Wound

Electrical Characteristics

Self Resonant Frequency	2.2 GHz
Inductance	.039 μ H
Current Rating (Max)	600 mA
DC Resistance	.25 Ω
Passive Component Tolerance	5 %

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Dimensions

Product Length	1.8 mm[.07 in]
Product Width	1.12 mm[.044 in]
Product Height	1.02 mm[.04 in]

Usage Conditions

Operating Temperature Range	-40 – 125 $^{\circ}$ C[-40 – 257 $^{\circ}$ F]
-----------------------------	--

Packaging Features



Packaging Method	Taped & Reeled
------------------	----------------

Other

Inductor Quality Factor	40
-------------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 4-1879023-8
3650 1008 10uH 5% 2K RL


TE Part # 5-1624113-2
3650 0805 0.22uH 5% 2K RL

TE Part # 4-1624112-4
3650 0402 16nH 5% 2K RL



TE Part # 1624112-8
3650 0603 68nH 5% 2K RL



Also in the Series | [Sigma 3650](#)



Customers Also Bought



Documents

[Product Drawings](#)
[3650 0603 39nH 5% 2K RL](#)

English

[CAD Files](#)
[3D PDF](#)

3D



Customer View Model

[ENG_CVM_CVM_1624112-6_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1624112-6_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1624112-6_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[Low Inductance, High Frequency Chip Inductors - Type 3650 Series](#)

English