1376113-1 ✔ ACTIVE


AMP | 0.64/025 Connector System

TE Internal #: 1376113-1

Vertical, Wire-to-Board, 40 Position, 2 Row, 2.2mm [.087in] Centerline, Tin (Sn), Printed Circuit Board, Signal, Natural, 0.64/025 Connector System

View on TE.com >

Automotive Parts > Automotive Connectors > Automotive Headers > High Pin Count Header



PCB Mount Orientation: **Vertical**

Termination Method to PCB: **Through Hole - Solder**

Sealable: **No**

Centerline (Pitch): **2.2 mm [.087 in]**

Connector System: **Wire-to-Board**

All High Pin Count Header (49)

Features

Product Type Features

Connector Product Type	Connector Assembly
Mixed & Hybrid Header	No
Header Type	Fully Shrouded
Connector Shape	Rectangular
Sealable	No
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Signal Positions	40
Number of Sections	1
PCB Mount Orientation	Vertical
Number of Positions	40
Number of Rows	2

Electrical Characteristics

Operating Voltage	12 VDC
Voltage Rating (Max)	12 VDC
Nominal Voltage Architecture	12 V

Body Features

Primary Product Color	Natural

Contact Features

Mating Tab Width	.64 mm[.025 in]
Mating Tab Thickness	.64 mm[.025 in]
Contact Type	Tab
Contact Mating Area Plating Material	Tin (Sn)

Termination Features

Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Interface
PCB Mount Retention	Without
Mounting Holes	With
Mating Alignment	With
PCB Mount Alignment	Without

Housing Features

Centerline (Pitch)	2.2 mm[.087 in]

Dimensions

Connector Width	15.3 mm[.602 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Length	49.4 mm[1.94 in]
Profile Height from PCB	23.4 mm[.921 in]

Usage Conditions

Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C[212 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Operation/Application

Shielded	No
Circuit Application	Signal

Packaging Features

Packaging Quantity	9
Packaging Method	Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM, HOUSING




TE Part # 1318695-1
025 IDC LOCK HSG 40P




TE Part # 1376114-1
025 CAP HSG V-TYPE 40P

Also in the Series | 0.64/025 Connector System




Automotive Connector Locks & Position Assurance(1)



Automotive Housings(180)

Automotive Signal & Power Connector Housings(180)

Connector Seals & Cavity Plugs(2)



Other Automotive Connector Accessories(5)

Customers Also Bought



TE Part #CAT-SIGH262
Signal Header



TE Part #2013029-4
0.50 SERIES 24POS CAP ASSY(SMT TYPE)




TE Part #1-2295435-1
36POS,HYBRID,HDR ASSY,180DEG, SMD




TE Part #1-2295435-2
36POS,HYBRID,HDR ASSY,180DEG, SMD

TE Part #1376111-8
025 24POS CAP ASSY V 3 Au



TE Part #7-1447178-1
FS2N76.2A20 (FSN-73A-20)

TE Part #1554558-1
0.64/1.5 13POSITION CAP ASSY S



TE Part #1871806-1
0.50 SERIES 40POS CAP ASSEMBLY (SMT TYPE)

TE Part #1939082-2
0.5/1.5 HYBRID 16POS SMT CAP ASSY

Documents

Product Drawings

025 CAP ASSY V-TYPE 40P

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1376113-1_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1376113-1_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1376113-1_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Crimping of 025 Receptacle Contact

Japanese

Application Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

English

Instruction Sheet (non U.S.)

Japanese

Agency Approvals

Agency Approval Document

English