

1376689-1 ✓ ACTIVE

AMP | AMP Auto Squib Products

TE Internal #: 1376689-1

Black, Locking Device, PBT GF30, -30 – 80 °C [-22 – 176 °F], AMP Auto Squib Products

[View on TE.com >](#)



Automotive Parts > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance



Primary Product Color: **Black**

Connector & Contact Retention Accessory Type: **Locking Device**

Primary Product Material: **PBT GF30**

Operating Temperature Range: **-30 – 80 °C [-22 – 176 °F]**

Features

Product Type Features

Sealable	No
Connector & Contact Retention Accessory Type	Locking Device

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF30

Usage Conditions

Operating Temperature Range	-30 – 80 °C[-22 – 176 °F]
-----------------------------	---------------------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Bag
Packaging Quantity	500

Other

Serviceable	Yes
-------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts

 <p>TE Part # 1376688-1 11DIA SQUIB SLIM PLUG HSG YELL</p>	 <p>TE Part # 1376688-3 11DIA SQUIB SLIM PLUG HSG ORNG</p>	 <p>TE Part # 1376688-2 11DIA SQUIB SLIM PLUG HSG YELL</p>
---	---	---

Also in the Series | AMP Auto Squib Products

 <p>Automotive Connector Locks & Position Assurance(8)</p>	 <p>Automotive Housings(12)</p>	 <p>Automotive Signal & Power Connector Housings(12)</p>	 <p>Other Automotive Connector Accessories(24)</p>
---	---	---	---

Customers Also Bought



Documents

Product Drawings

11DIA SQUIB SLIM LOCK BUTTON

English

CAD Files

Customer View Model

[ENG_CVM_1376689-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1376689-1_O.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1376689-1_O.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

11DIA SQUIB CONNECTOR CHECKER

English

11DIA SQUIB CONNECTOR CHECKER

Japanese

SQUIB Connector 11DIA

Japanese

Product Specification

Japanese



SQUIB Connector 11DIA

Japanese

Product Specification

Japanese

Instruction Sheets

11dia squib connector checker

Japanese

Instruction Sheet (non U.S.)

Japanese

Instruction Sheet (non U.S.)

English

11DIA SQUIB CONNECTOR SLIM TYPE

English