




Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **Natural**

Primary Product Material: **Polyester**

Number of Positions: **16**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Product Profile	Standard
Connector Cover Type	Strain Relief Cover

Configuration Features

Number of Positions	16
---------------------	----

Body Features

Primary Product Color	Natural
Primary Product Material	Polyester

Mechanical Attachment

Strain Relief	With
---------------	------

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
--------------------	------------------

Usage Conditions

Compatible With IDC Installation Type Connector	Closed End
Operating Temperature (Max)	105 °C[221 °F]



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 4-640605-6
16P MTA156 CONN ASSY 20AWG LF



TE Part # 4-643819-6
16P MTA156 CONN ASSY 22AWG LF



TE Part # 641623-1
MTA156 KEYING PLUG (10/STRIP)



TE Part # 1-640251-6
16P SL156 HSG W/O LCK RAMP



TE Part # 1-640387-6
16P MTA156 HDR ASSY SQ R/A

TE Part # 4-644769-6
16P MTA156 HDR ASSY R/A SQ LF

TE Part # 4-641148-6
16P MTA156 ASSY 18AWG ORA LF

TE Part # 4-644460-6
16P MTA156 CONN ASSY 18AWG ORA

TE Part # 1-640388-6
16P MTA156 HDR ASSY RN STR F/L

TE Part # 1-644752-6
16P MTA156 HDR ASSY SQ STR F/L

TE Part # 1-644751-6
16P MTA156 HDR ASSY R/A

TE Part # 4-640427-6
16P MTA156 CONN ASSY 20AWG YEL

TE Part # 4-640433-6
16P MTA156 CONN ASSY 22AWG RED

TE Part # 4-640601-6
16P MTA156 CONN ASSY 22AWG LF

TE Part # 4-641120-6
16P MTA156 HDR ASSY FL/ST LF

TE Part # 4-641210-6
16P MTA156 HDR FLRA FB 30AU LF

TE Part # 1-640389-6
16P MTA156 HDR ASSY SQ R/A F/L

TE Part # 1-640445-6
16P MTA156 HDR ASSY FL/STR SN

TE Part # 1-644753-6
16P MTA156 HDR ASSY RN STR F/L

TE Part # 1-1744194-6
16P MTA156 HDR ASSY FL/STR SN


Also in the Series | **MTA 156**

Connector Caps & Covers(89)

Connector Contacts(4)

Connector Hardware(2)

Insertion & Extraction Tools(1)




PCB Headers & Receptacles(677)



Power Contacts(3)



Rectangular Power Connectors(1178)



Wire-to-Board Headers & Receptacles (677)

Customers Also Bought



TE Part #88976-5
CONTACT,PIN,15AU,FFC




TE Part #206306-1
23-37 RECEPT REV SEX




TE Part #487378-9
010 HOUSING FFC RCPT 100CL SR



TE Part #3-640431-4
04P MTA156 CONN ASSY 18AWG
ORA




TE Part #640551-4
04P MTA156 COVER



TE Part #1-640551-0
10P MTA156 COVER



TE Part #770985-3
MINI UMNL PIN 26-22AWG AU LP



TE Part #1-796640-4
14 POS 5.0 MM R/A PLUG,TRM BLK



TE Part #1658611-4
09 POS HDF PLUG, AP, LEAD FREE



TE Part #5205207-1
HD RECPT ASSY SIZE 3

Documents

Product Drawings
16P MTA156 COVER

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_1-640551-6_G.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-640551-6_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-640551-6_G.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-640551-6_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-640551-6_L.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-640551-6_L.2d_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

Japanese

[Application Specification](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

Japanese