




Antennas



Antenna Product Type: **Antenna**

Features

Product Type Features

Antenna Product Type	Antenna
----------------------	---------

Configuration Features

Antenna Style	PCB
---------------	-----

Electrical Characteristics

Impedance	50 Ω
Antenna Operation	Passive
VSWR (Max)	<2.5:1

Signal Characteristics

Frequency Band	880 – 960 MHz, 1710 – 1880 MHz
Gain (Max)	2 dB

Body Features

Product Weight	2 g[.0705 oz]
----------------	---------------

Mechanical Attachment

Polarization	Linear
--------------	--------

Dimensions

Product Width	15.2 mm[.598 in]
Product Length	38.25 mm[1.5 in]
Product Height	1.57 mm[.062 in]

Operation/Application

Wireless Standard	EU Dual Band
-------------------	--------------

Product Availability

--	--



Applicable Region	EU
-------------------	----

Packaging Features

Packaging Method	Bag & Box
------------------	-----------

Other

Precision Level	Standard
-----------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2019 (197) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought





TE Part #CAT-R21-73106549

Bulbous Heat Shrink Boots: Lipped, Right Angle



TE Part #154717-6

PL 250 REC TERMINAL 14-11 AWG PTPB



TE Part #1-1703543-0

2POS,TAB 2.8X0.8,TAB HSG,ASSY

Documents

- CAD Files

Customer View Model

ENG_CVM_CVM_1513434-1_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1513434-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1513434-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

- Datasheets & Catalog Pages

PCB ANTENNA

English