1-643067-8 ✔ ACTIVE

MTA 156

TE Internal #: 1-643067-8


Strain Relief Cover, White, Nylon, 18 Position, MTA 156

View on TE.com >

Connectors > Connector Accessories > Connector Caps & Covers







Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **White**

Primary Product Material: **Nylon**

Number of Positions: **18**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Product Profile	Standard
Connector Cover Type	Strain Relief Cover

Configuration Features

Number of Positions	18

Body Features

Primary Product Color	White
Primary Product Material	Nylon

Mechanical Attachment

Strain Relief	With

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]

Usage Conditions

Compatible With IDC Installation Type Connector	Closed End
Operating Temperature (Max)	105 °C[221 °F]

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Industry Standards

UL Flammability Rating	UL 94V-2

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts



TE Part # 4-640605-8
18P MTA156 CONN ASSY 20AWG LF



TE Part # 1-1744194-8
18P MTA156 HDR ASSY FL/STR SN




TE Part # 4-641209-8
18P MTA156 HDR ASSY FL ST LF



TE Part # 644960-1
18P MTA156 HDR ASY WO4,8,12,16




TE Part # 1-640387-8
18P MTA156 HDR ASSY SQ R/A




TE Part # 4-644615-8
18P MTA156 POL HDR ASSY LF




TE Part # 4-644617-8
18P MTA156 HDR ASY PO RA FB LF




TE Part # 4-640602-8
18P MTA156 CONN ASSY 24AWG LF




TE Part # 4-644633-8
18P MTA156 HDR ASSY R/A LF



TE Part # 4-640428-8
18P MTA156 CONN ASSY 22AWG RED




TE Part # 4-644460-8
18P MTA156 CONN ASSY 18AWG ORA



TE Part # CAT-103156-WBHSM
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156



TE Part # 4-641207-8
18P MTA156 HDR ASSY FL RA LF



TE Part # 1-640383-8
18P MTA156 HDR ASSY STR SQ SN



TE Part # 1-644752-8
18P MTA156 HDR ASSY SQ STR F/L




TE Part # 1-640445-8
18P MTA156 HDR ASSY FL/STR SN




TE Part # 1-640385-8
18P MTA156 HDR ASSY SQ R/A



TE Part # 1-640388-8
18P MTA156 HDR ASSY RN STR F/L



TE Part # 4-643819-8
18P MTA156 CONN ASSY 22AWG LF



TE Part # 4-640427-8
18P MTA156 CONN ASSY 20AWG YEL


Also in the Series | MTA 156



Connector Caps & Covers(89)



Connector Contacts(4)




Connector Hardware(2)



Power Contacts(3)



Rectangular Power Connectors(1178)



Standard Rectangular Connectors(667)



Wire-to-Board Connector Assemblies & Housings(594)


Customers Also Bought




TE Part #35109
TERMINAL,PIDG R 12-10 10



TE Part #4-640428-8
18P MTA156 CONN ASSY 22AWG RED



TE Part #3-641126-3
03P MTA100 HDR ASY FL/STR LF



TE Part #643067-6
06P MTA156 MOLDED COVER



TE Part #881545-1
SHUNT LP W/HANDLE 2POS 15AU



TE Part #1-1469492-1
MULTIGIG RT 9MM GUIDE/ESD 0 DEG



TE Part #1-1469492-3
MULTIGIG RT 9MM GUIDE/ESD 90 DEG



TE Part #1-1623925-5
CFR100 5% 1K0



TE Part #2-1761603-6
IDC LOW PRO HDR 16P VERT BLUE

TE Part #4-1393159-6
20C314=SPRING,HOLD,DOWN,KUP

Documents

Product Drawings

18P MTA156 MOLDED COVER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-643067-8_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-643067-8_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-643067-8_P.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_1-643067-8_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_1-643067-8_G.3d_igs.zip

English

Customer View Model

ENG_CVM_1-643067-8_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese

Instruction Sheets

Instruction Sheet (U.S.)

English