



TE Internal #: 1-5645955-1
 4.67 mm [.184 in] Socket Length, 1.32 mm [.052 in] PCB Hole, Bullet
 Nose, .081 – .326 mm² Wire, 28 – 22 AWG, Cable-to-Board, Pin
 Sockets

[View on TE.com >](#)

Connectors > Socket Connectors > Pin Sockets > Miniature Spring Sockets: Bullet Nose, Beryllium Copper, 4A



Socket Length: **4.67 mm [.184 in]**
 PCB Hole Diameter: **1.32 mm [.052 in]**
 Socket Sleeve Style: **Bullet Nose**
 Wire Size: **28 – 22 AWG**

[All Miniature Spring Sockets: Bullet Nose, Beryllium Copper, 4A \(14\)](#)

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Socket Sleeve Style	Bullet Nose
Connector System	Cable-to-Board
Sealable	No

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Sleeve Plating Material	Tin
Sleeve Material	Copper

Contact Features

Contact Spring Plating Material	Tin
Contact Base Material	Beryllium Copper
Contact Mating Area Plating Material Thickness	2.54 µm
Contact Spring Plating Thickness	2.54 µm[30 µin]
Contact Current Rating (Max)	4 A

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Method to Wire & Cable	Solder



Insertion Method	Hand/Semi-Automatic/Automatic
------------------	-------------------------------

Dimensions

PCB Thickness (Recommended)	.79 – 3.18 mm [.031 – .125 in]
Socket Length	4.67 mm [.184 in]
PCB Hole Diameter	1.32 mm [.052 in]
Wire Size	28 – 22 AWG
Mating Pin Diameter Range	.36 – .66 mm [.014 – .026 in]

Usage Conditions

Operating Temperature Range	-65 – 125 °C [-85 – 257 °F]
-----------------------------	-----------------------------

Operation/Application

Solder Process Feature	Anti-Flux
Circuit Application	Power & Signal

Packaging Features

Packaging Method	Reel
Packaging Quantity	10000

Other

Spring Material	Beryllium Copper
-----------------	------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-5645955-2
SOCKET,MIN-SPR B-N SN-AU SER-2


Customers Also Bought



TE Part #1-215297-0
10P HV100 REC CON. TE, 7.0MM



TE Part #282830-4
TERMI-BLOK PLUG 90&180 4P. 5




TE Part #1-1393219-7
PE514005




TE Part #2-1416010-6
RE034012




TE Part #6-1601046-1
231-101-000=WIRE2WIRE,STD,SMZ




TE Part #4-2307345-2
STD RANGE WIRE TO TAB,080X020, SMZ



TE Part #EQ08993001
FLDWC0311-24-9CK1500



TE Part #1601037-4
131-083-010=TAB,059X032,STDSMZ



Documents

Product Drawings

[SOCKET,MIN-SPR B-N SN-SN SER-2](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1-5645955-1_O.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-5645955-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-5645955-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English