




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Receptacle**
Connector System: **Board-to-Board**
Number of Positions: **190**
Centerline (Pitch): **.64 mm, 24 mm [.945 in]**
PCB Mount Orientation: **Vertical**

Features

Product Type Features

Ground Feature Type	Ground Bus
PCB Connector Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	95
Number of Signal Positions	190
Number of Power Positions	5
Stackable	Yes
Number of Positions	190
PCB Mount Orientation	Vertical
Board-to-Board Configuration	Parallel

Electrical Characteristics

Operating Voltage	5 VDC
Impedance	50 Ω



Insulation Resistance	2 MΩ
Dielectric Withstanding Voltage (Max)	500 VAC

Signal Characteristics

Data Rate	10 Gb/s
Differential Signaling	Yes

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material Finish	Matte
PCB Contact Termination Area Plating Material Thickness	3.81 – 6.35 μm[150 – 250 μin]
Contact Shape & Form	Dual Beam
Contact Layout	Inline
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	.76 μm[29.92 μin]
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Socket
Contact Current Rating (Max)	11.5 A

Termination Features

Rectangular Termination Post & Tail Width	.53 mm[.021 in]
Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Termination Method to PCB	Surface Mount

Mechanical Attachment

Mating Retention	With
PCB Mount Alignment Type	Locating Posts
Connector Mounting Type	Board Mount
Mating Alignment	Without
PCB Mount Alignment	With
PCB Mount Retention	With

Housing Features

--	--



Mating Entry Location	Top
Centerline (Pitch)	.64 mm, 24 mm [.945 in]
Housing Material	Matte

Dimensions

Connector Width	6.9 mm [.272 in]
Connector Height	5.99 mm [.236 in]
Connector Length	76.2 mm [3 in]
Stack Height	6.6 mm, 9 mm, 10.92 mm, 12.57 mm, 17.96 mm, 18.75 mm, 20 mm, 22.86 mm [.9 in]
PCB Thickness (Recommended)	1.57 mm [.8 in]

Usage Conditions

Operating Temperature Range	-55 – 125 °C [-67 – 257 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Listed
Compatible With Approved Standards Products	CSA 1195944, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	252
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC













Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 5767149-5 MICT,495,PLG,190,TAPE,CAP	 TE Part # 5767111-5 MICT,PLG,190,ASY,.025 TAPE PKG	 TE Part # 5767127-5 MICT,REC,190,ASY,.025 TAPE PKG	 TE Part # 5767056-5 MICT,260,PLUG,190,ASSY,PDNI
 TE Part # 1-5767005-2 MICT,495PLUG,190,ASSY,.025,REC	 TE Part # 5767042-5 MICT,738PLUG,190,ASSY,.025,EXT	 TE Part # 1-5767149-2 MICTOR PLUG ASSY IN TAPE & REE	 TE Part # 1-5767118-2 MICT,PLG,190,ASY,.025,TAPE PKG
 TE Part # 5767006-5 MICT,R/APLUG,190,ASY,.025,.062	 TE Part # 5767120-5 MICT,495PLG,190,ASY,.025,AUPLT	 TE Part # 1-5767007-2 MICT,260PLUG,190,ASSY,.025,REC	 TE Part # 5767039-5 MICTOR,RA PLUG,190,.093PCB,ASY



Customers Also Bought



Documents

Product Drawings
MICT,REC,190,ASY,.025 TAPE PKG
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-5767115-2_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-5767115-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-5767115-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English