




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Partially Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Loaded Positions	2
PCB Mount Orientation	Vertical
Number of Positions	2
Number of Rows	1
Number of Power Positions	2

Electrical Characteristics

--	--



Operating Voltage	250 VDC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1 µm[39.37 µin]
PCB Contact Termination Area Plating Material Thickness	3.048 µm[120 µin]
Contact Layout	Inline
Contact Mating Area Length	7.7 mm[.303 in]
Contact Base Material	Brass
Contact Mating Area Plating Material	Tin (Sn)
Contact Mating Area Plating Material Thickness	3.048 µm[120 µin]
Contact Type	Tab
Contact Current Rating (Max)	8 A
PCB Contact Termination Area Plating Material	Tin

Termination Features

Termination Post & Tail Length	3.69 mm[.145 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Retention Type	Locking Tab
PCB Mount Alignment Type	Pegs
PCB Mount Alignment	With
Mating Retention	With
PCB Mount Retention	Without
Connector Mounting Type	Board Mount
Mating Alignment	Without

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
Housing Material	Nylon

Dimensions

Connector Width	8.6 mm[.339 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]



Connector Height	9.4 mm[.37 in]
Connector Length	7.92 mm[.312 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	GWT 750°C (Without Flame)
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-1744524-2
EP 12P HEADER ASY NO 2,6 PINS

TE Part # 2-1744524-5
EP 05P HEADER ASY NO 2,3,4 PIN

TE Part # 1-1744524-1
EP 11P HEADER ASY NO 6,10 PINS

TE Part # 1-1744429-6
3.96 EP HDR ASSY 6P W/PEGS, GW, NO PIN 3

TE Part # 1-1744429-9
3.96 EP HDR ASSY 9P W/PEGS, GW, NO PIN 3

TE Part # 1-1744524-0
EP 10P HEADER ASY NO 8 PIN

TE Part # 1744544-2
EP II TPA 02P, BLACK

TE Part # 1-1123722-2
3.96 EP PLUG HSG 2P(NATURAL)

TE Part # 2-1744435-8
EP 08P V-HDR ASY NO 3 PIN

Also in the Series | Economy Power

Connector Contacts(13)

Connector Hardware(2)

Insertion & Extraction Tools(1)


PCB Headers & Receptacles(463)



[Power Contacts\(7\)](#)




[Rectangular Power Connectors\(547\)](#)



[Wire-to-Board Headers & Receptacles \(463\)](#)


Customers Also Bought




TE Part #4-794630-8
[18P MICRO MNL ASSY,VRT,HDR,LF](#)




TE Part #7-1625892-2
[3W SM M/OX 5% 82K](#)




TE Part #1744429-3
[3.96 EP HDR ASSY 3P W/PEGS, GW](#)




TE Part #1744429-5
[3.96 EP HDR ASSY 5P W/PEGS, GW](#)




TE Part #2029265-2
[2P VAL-U-LOK VRTHDR W/PGS GW](#)




TE Part #2029265-8
[8P VAL-U-LOK VRTHDR W/PGS GW](#)




TE Part #1-2029265-2
[12P VAL-U-LOK VRTHDR W/PGS GW](#)



TE Part #6-2176421-3
[TLRP 2512 2.0W R060 1% 50PPM 4K RL](#)



TE Part #9-2176480-3
[RA73F 1J 4K99 0.1% 5K RL](#)



TE Part #1-1721260-1
[OJ-SH-112LMH2](#)

Documents

[CAD Files](#)

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_1744429-2_D.2d_dxf.zip](#)

[English](#)

[Customer View Model](#)

[ENG_CVM_CVM_1744429-2_D.3d_igs.zip](#)

1744429-2

PCB Mount Header, Vertical, Wire-to-Board, 2 Position, 3.96 mm [.156 in] Centerline, Partially Shrouded, Tin (Sn), Economy Power



English

Customer View Model

[ENG_CVM_CVM_1744429-2_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Economy Power II \(EP II\) Glow Wire test compliant connectors](#)

English

[7-1773458-5_ECONOMY_POWER_QRG](#)

English

Product Specifications

[Application Specification](#)

Japanese

Agency Approvals

[UL Report](#)

English