




Automotive Parts > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: 126

Primary Product Color: Black

Protection & Strain Relief Accessory Type: Wire Cover

Primary Product Material: PBT

Strain Relief: Without

Features

Product Type Features

Sealable	Yes
Protection & Strain Relief Accessory Type	Wire Cover

Configuration Features

Number of Positions	126
---------------------	-----

Body Features

Primary Product Color	Black
Primary Product Material	PBT

Mechanical Attachment

Strain Relief	Without
---------------	---------

Usage Conditions

Operating Temperature (Max)	140 °C[284 °F]
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]

Packaging Features

Packaging Method	Bag
------------------	-----



Packaging Quantity

120

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | [0.64/025 Connector System](#)




Automotive Connector Locks & Position Assurance(1)



Automotive Housings(174)



Automotive Seals & Cavity Plugs(2)



Other Automotive Connector Accessories(4)

Customers Also Bought



TE Part #170454-2
PL 250 AM REC 18-14 0.40 X 21 PRE-TPBR




TE Part #7-1452665-3
MCON 1.2 LL REC SWS AG



TE Part #CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM, HOUSING



TE Part #1813271-1
SEALED MT2 PLUG HOUSING ASSEMBLY



TE Part #1554740-2
0.50/1.0 SEALED WIRE COVER 140



TE Part #2822015-1
0.5 SERIES CONN 30POS PLUG ASSY

Documents

Product Drawings

SEALED EFI ECU 126P PLUG WIRE COVER

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1746941-1_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1746941-1_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1746941-1_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Product Specifications

Product Specification

Japanese

Product Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

English

Instruction Sheet (non U.S.)

Japanese