




Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **Natural**

Primary Product Material: **Polyester**

Number of Positions: **15**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Product Profile	Standard
Connector Cover Type	Strain Relief Cover

Configuration Features

Number of Positions	15
---------------------	----

Body Features

Primary Product Color	Natural
Primary Product Material	Polyester

Mechanical Attachment

Strain Relief	With
---------------	------

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
--------------------	------------------

Usage Conditions

Compatible With IDC Installation Type Connector	Closed End
Operating Temperature (Max)	105 °C[221 °F]



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 4-641439-5
15P MTA156 PST CON ASSY LF




TE Part # 4-640605-5
15P MTA156 CONN ASSY 20AWG LF




TE Part # 1-644751-5
15P MTA156 HDR ASSY R/A




TE Part # 1-640384-5
15P MTA156 HDR ASSY STR RND SN




TE Part # 4-641120-5
15P MTA156 HDR ASSY FL/ST LF




TE Part # 4-644766-5
15P MTA156 HDR ASSY STR SQ LF




TE Part # 4-644769-5
15P MTA156 HDR ASSY R/A SQ LF




TE Part # 4-641210-5
15P MTA156 HDR FLRA FB 30AU LF




TE Part # 4-643819-5
15P MTA156 CONN ASSY 22AWG LF




TE Part # 4-641208-5
15P MTA156 HDR ASSY FL ST LF




TE Part # 4-640427-5
15P MTA156 CONN ASSY 20AWG YEL




TE Part # 4-647476-5
15P MTA156 PSTD CONN 18AWG LF




TE Part # 4-644460-5
15P MTA156 CONN ASSY 18AWG ORA




TE Part # 4-640428-5
15P MTA156 CONN ASSY 22AWG RED




TE Part # 4-641119-5
15P MTA156 HDR ASSY FL/ST LF



TE Part # 4-641437-5
15P MTA156 PSTD CONN ASSY RED




TE Part # 4-643817-5
15P MTA156 CONN ASSY 18AWG ORA



TE Part # CAT-103156-WBHS
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156



TE Part # 1-770996-5
15P SL 156 HSG W/TABS W/O LR




TE Part # 1-640385-5
15P MTA156 HDR ASSY SQ R/A


Also in the Series | **MTA 156**




Connector Caps & Covers(89)



Connector Contacts(4)



Connector Hardware(2)



Power Contacts(3)



[Rectangular Power Connectors\(1178\)](#)



[Standard Rectangular Connectors\(667\)](#)



[Wire-to-Board Connector Assemblies & Housings\(594\)](#)

Customers Also Bought



TE Part #60024-2
[RING CRIMP TAB 18-14 AWG TPBR](#)




TE Part #3-640426-4
[04P MTA156 CONN ASSY 18AWG ORA](#)




TE Part #4-640428-2
[12P MTA156 CONN ASSY 22AWG RED](#)




TE Part #4-640440-2
[12P MTA100 CONN ASSY 22AWG RED](#)




TE Part #1-640455-2
[12P MTA100 HDR ASSY SQ R/A POL](#)



TE Part #1-640550-2
[12P MTA100 COVER](#)



TE Part #640551-4
[04P MTA156 COVER](#)



TE Part #644752-4
[04P MTA156 HDR ASSY SQ STR F/L](#)



TE Part #1-644752-0
[10P MTA156 HDR ASSY SQ STR F/L](#)



TE Part #794220-1
[MINI UMN2 PIN 22-18 AWG SN](#)

Documents

[Product Drawings](#)
[15P MTA156 COVER](#)

English

[CAD Files](#)
[3D PDF](#)

3D

[Customer View Model](#)
[ENG_CVM_CVM_1-640551-5_G.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_1-640551-5_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-640551-5_G.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-640551-5_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-640551-5_L.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-640551-5_L.2d_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

Japanese

[Application Specification](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

Japanese