



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **White**

Primary Product Material: **Nylon**

Number of Positions: **13**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Product Profile	Standard
Connector Cover Type	Strain Relief Cover

Configuration Features

Number of Positions	13
---------------------	----

Body Features

Primary Product Color	White
Primary Product Material	Nylon

Mechanical Attachment

Strain Relief	With
---------------	------

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
--------------------	------------------

Usage Conditions

Compatible With IDC Installation Type Connector	Closed End
Operating Temperature (Max)	105 °C[221 °F]



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 4-644465-3
13P MTA156 CONN ASSY 18AWG
ORA




TE Part # 4-640602-3
13P MTA156 CONN ASSY 24AWG LF




TE Part # 1-640384-3
13P MTA156 HDR ASSY STR RND SN



TE Part # CAT-103156-WBHSM
Receptacle Housing: Wire-to-Board,
with Mating Alignment, SL156



TE Part # 1-640445-3
13P MTA156 HDR ASSY FL/STR SN



TE Part # 4-644769-3
13P MTA156 HDR ASSY R/A SQ LF




TE Part # 1-770996-3
13P SL 156 HSG W/TABS W/O LR




TE Part # 1-640385-3
13P MTA156 HDR ASSY SQ R/A




TE Part # 1-640388-3
13P MTA156 HDR ASSY RN STR F/L




TE Part # 641533-1
02P MTA156 CONN HSG,END CAP



TE Part # 4-641207-3
13P MTA156 HDR ASSY FL RA LF




TE Part # 4-640599-3
13P MTA156 CONN ASSY 18AWG ORA



TE Part # 4-640426-3
13P MTA156 CONN ASSY 18AWG ORA




TE Part # 1-644751-3
13P MTA156 HDR ASSY R/A




TE Part # 1-641119-3
13P MTA156 HDR ASSY FL/ST 15AU



TE Part # 4-641120-3
13P MTA156 HDR ASSY FL/ST LF




TE Part # 4-643819-3
13P MTA156 CONN ASSY 22AWG LF



TE Part # 4-643818-3
13P MTA156 CONN ASSY 20AWG YEL



TE Part # 4-640429-3
13P MTA156 CONN ASSY 24AWG WHT



TE Part # 4-640433-3
13P MTA156 CONN ASSY 22AWG RED

Also in the Series | **MTA 156**



Connector Caps & Covers(89)



Connector Contacts(4)




Connector Hardware(2)



Power Contacts(3)



Rectangular Power Connectors(1178)



Standard Rectangular Connectors(667)



Wire-to-Board Connector Assemblies & Housings(594)


Customers Also Bought



TE Part #800248-SF
FN382-6-22




TE Part #1-640388-3
13P MTA156 HDR ASSY RN STR F/L



TE Part #3-640427-5
05P MTA156 CONN ASSY 20AWG YEL



TE Part #4-640427-3
13P MTA156 CONN ASSY 20AWG YEL



TE Part #643067-5
05P MTA156 MOLDED COVER



TE Part #4-1625890-9
2W SM M/OX 5% 3R9



TE Part #1676251-2
RN 0805 210R 0.1% 10PPM 1KRL



TE Part #8-1879130-1
RN 0402 4K99 0.1% 10PPM 5K RL



TE Part #1-2176411-1
1/2W SM M/OX 5% 30K



TE Part #1-2351886-0
10POS TB HDR 180 DEG, PITCH 3.5, TL3.4mm

Documents

Product Drawings

13P MTA156 MOLDED COVER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-643067-3_P.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-643067-3_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-643067-3_P.3d_stp.zip](#)

English

[3D PDF](#)

English

Customer View Model

[ENG_CVM_1-643067-3_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_1-643067-3_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-643067-3_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

Japanese

[Application Specification](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

Japanese

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English