1-643067-6 ✔ ACTIVE

MTA 156

TE Internal #: 1-643067-6


Strain Relief Cover, White, Nylon, 16 Position, MTA 156

View on TE.com >

Connectors > Connector Accessories > Connector Caps & Covers







Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **White**

Primary Product Material: **Nylon**

Number of Positions: **16**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Product Profile	Standard
Connector Cover Type	Strain Relief Cover

Configuration Features

Number of Positions	16

Body Features

Primary Product Color	White
Primary Product Material	Nylon

Mechanical Attachment

Strain Relief	With

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]

Usage Conditions

Compatible With IDC Installation Type Connector	Closed End
Operating Temperature (Max)	105 °C[221 °F]

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Industry Standards

UL Flammability Rating	UL 94V-2

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts



TE Part # 4-640605-6
16P MTA156 CONN ASSY 20AWG LF




TE Part # 1-643067-2
12P MTA156 MOLDED COVER




TE Part # 4-643819-6
16P MTA156 CONN ASSY 22AWG LF




TE Part # 1-640251-6
16P SL156 HSG W/O LCK RAMP



TE Part # 1-640387-6
16P MTA156 HDR ASSY SQ R/A



TE Part # 4-644769-6
16P MTA156 HDR ASSY R/A SQ LF




TE Part # 4-641148-6
16P MTA156 ASSY 18AWG ORA LF




TE Part # 4-640602-6
16P MTA156 CONN ASSY 24AWG LF




TE Part # 1-640383-6
16P MTA156 HDR ASSY STR SQ SN




TE Part # CAT-103156-WBHSM
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156



TE Part # 1-640385-6
16P MTA156 HDR ASSY SQ R/A




TE Part # 1-641119-6
16P MTA156 HDR ASSY FL/ST 15AU




TE Part # 641533-1
02P MTA156 CONN HSG,END CAP




TE Part # 4-643817-6
16P MTA156 CONN ASSY 18AWG LF




TE Part # 4-640426-6
16P MTA156 CONN ASSY 18AWG ORA




TE Part # 4-641119-6
16P MTA156 HDR ASSY FL/ST LF



TE Part # 4-641209-6
16P MTA156 HDR ASSY FL ST LF



TE Part # 4-640599-6
16P MTA156 CONN ASSY 18AWG ORA



TE Part # 4-641208-6
16P MTA156 HDR ASSY FL ST LF



TE Part # 1-640389-6
16P MTA156 HDR ASSY SQ R/A F/L


Also in the Series | MTA 156



Connector Caps & Covers(89)




Connector Contacts(4)



Connector Hardware(2)



Insertion & Extraction Tools(1)




PCB Headers & Receptacles(677)



Power Contacts(3)



Rectangular Power Connectors(1178)



Wire-to-Board Headers & Receptacles (677)

Customers Also Bought



TE Part #CSA265N00450001000
940 PLUG



TE Part #ASA558N00610235000
623 PLUG



TE Part #ASA035N00410100000
623 PLUG, SPEEDTEC



TE Part #BSA108N00590236000
923 PLUG, SHORT



TE Part #AKA047N0085051A000
617 EXTENSION, SPEEDTEC




TE Part #ADA558N00000151000
623 BULKHEAD CONNECTOR



TE Part #344270-1
4 WAY REC.HSG. SIL. SEAL ECONO



TE Part #3-1623773-0
C10 68R 5% (LOOSE)



TE Part #4-6447189-2
FSN-24A-10

TE Part #61-0020-011-100
contact pin d=1 mm big pack 1000

Documents

Product Drawings

16P MTA156 MOLDED COVER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-643067-6_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-643067-6_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-643067-6_P.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_1-643067-6_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_1-643067-6_G.3d_igs.zip

English

Customer View Model

ENG_CVM_1-643067-6_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese

Instruction Sheets

Instruction Sheet (U.S.)

English