




Automotive Parts > Automotive Connectors > Automotive Housings > Timer Connector Housing



Nominal Voltage Architecture: 12 V, 24 V
Connector & Housing Type: **Housing for Male Terminals**
Number of Positions: 21
Sealable: **No**
Operating Temperature Range: -40 – 120 °C [-40 – 248 °F]

[All Timer Connector Housing \(436\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Male Terminals
Sealable	No
Primary Locking Feature	Integrated in Housing
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	21
Number of Rows	3

Electrical Characteristics

Operating Voltage	28 VDC
-------------------	--------



Nominal Voltage Architecture	12 V, 24 V
------------------------------	------------

Body Features

Cable Exit Angle	180 °
Primary Product Color	Green
Connector & Keying Code	A

Contact Features

Contact Size	2.8mm
Contact Type	Tab
Mating Tab Width	2.8 mm[.11 in]

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA GF
Centerline (Pitch)	5 mm[.197 in]

Dimensions

Product Width	35.45 mm[1.396 in]
Product Length	42.5 mm[1.673 in]
Connector Height	30.6 mm[1.205 in]

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
Operating Temperature (Max)	120 °C[248 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Bag
------------------	-----

Other

Serviceable	No
-------------	----



Connector Position Assurance Capable

No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 967635-1
2.0 KONT



TE Part # CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part # 1-967625-1
JR POW TIM 21P




TE Part # 8-968975-1
MCP2.8 GEH 21P



TE Part # 8-968975-2
MCP2.8 GEH ASSY 21P

Also in the Series | Timer Connector System



Automotive Connector Locks & Position Assurance(15)




Automotive Housings(186)



Automotive Seals & Cavity Plugs(32)



Automotive Signal & Power Connector Housings(136)



Other Automotive Connector Accessories(1)

Customers Also Bought




TE Part #130232
SOLIS R 12-10 10MM



TE Part #CAT-T4827-CH8172
Timer Connector Housing



TE Part #1-967630-3
FLACHSTE-GEH2,8 21P




TE Part #967635-1
2.0 KONT



TE Part #1-2141154-2
2POS,8MM HV,REC HSG,90DEG,ASSY, SEALED



TE Part #1-2358263-1
13POS,REC HSG ASSY,SLD,COD A



TE Part #284107-1
MULTILOCK CONN.070SRS.TAB CONT



TE Part #1-2325010-1
3POS,8MM HV,REC HSG,90 DEG, ASSY,SLD



Documents

Product Drawings

FLACHSTE-GEH2,8 21P

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-967630-4_E.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-967630-4_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-967630-4_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English