




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **4**
UL Flammability Rating: **UL 94V-0**
Primary Product Color: **Natural**

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Connector System	Wire-to-Board, Wire-to-Wire
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Receptacle
Contact Mating Retention	With

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Alignment	With

Housing Features



Housing Material	Nylon 6/6
------------------	-----------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2238207-3
187 FASTON,REC.,20-16 AWG,TPBR

TE Part # 2238173-3
250 FASTON,REC.,22-12 AWG,TPBR

TE Part # 2238196-3
FASTON 250 STD REC STR 18-14TPBR

Also in the Series | FASTON 187

Crimp Terminal Housings(117)

Insertion & Extraction Tools(6)

Insulation Boots & Sleeves(16)

PCB Terminals(131)

Quick Disconnects(404)

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(117)

Insulation Boots & Sleeves(16)

Magnet Wire Terminals(1)



PCB Terminals(131)



Quick Disconnects(404)




Splices(4)

Customers Also Bought



TE Part #42452-2
187 FASTON REC 20-16 AWG TPBR



TE Part #63306-2
250 FASTON REC 18-14 AWG TPBR




TE Part #63854-2
250 PL MKIII REC. 18-14AWG TPBR




TE Part #2-321518-1
TERMINAL,PG R 16-14HD 10




TE Part #521367-2
ULTRA-POD 250 ASSY REC 18-14 AWG TPBR



TE Part #521781-1
250 HSG. PL MKIII REC. 6.81mm 4P NAT




TE Part #1217114-2
187 PL MKIII REC. 18-14AWG TPBR



TE Part #1-1969614-0
10P RCPT VAL-U-LOK V0



TE Part #1969897-1
250 FASTON HSG.,REC.,5 POS,BLACK



TE Part #2238196-3
FASTON 250 STD REC STR 18-14TPBR

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1969898-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1969898-1_A.3d_igs.zip

1969898-1

Receptacle Terminal Housing, 4 Position, Natural, UL 94V-0, Nylon 6/6, Package, FASTON 187



English

Customer View Model

[ENG_CVM_CVM_1969898-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON TERMINALS \(INSULATED AND UNINSULATED\) - FULL CATALOG](#)

English