




TE Internal #: 2016694-2
 SMA Bulkhead to UMCC Cable Assembly, .1 m [.328 ft], Black
 Cable, 0 – 9 GHz, 50 ohm, FEP Jacket, 32 AWG, 1.13 mm [.044 in]
 Diameter, SMA Jack End A

[View on TE.com >](#)

Cable Assemblies > RF Cable Assemblies



Cable Assembly (End A): **SMA Jack**
 Cable Assembly (End B): **UMCC GEN 4 Plug**
 Cable Assembly Length: **.1 m [.328 ft]**
 Coax Cable Type: **1.13mm**
 Impedance: **50 Ω**

Features

Product Type Features

Cable Assembly (End A)	SMA Jack
Cable Assembly (End B)	UMCC GEN 4 Plug
Coax Cable Type	1.13mm
Cable Assembly Type	SMA Bulkhead to UMCC

Configuration Features

Number of Connectorized Ends	2
------------------------------	---

Electrical Characteristics

Insulation Resistance	300 MΩ
Operating Voltage	15 V
Impedance	50 Ω

Signal Characteristics

Velocity of Propagation	70 %
-------------------------	------

Body Features

Body Plating Material	Gold
-----------------------	------



Conductor Material	Copper
Strain Relief Type	HST
Conductor Plating Material	Gold
Jacket Material	FEP
Cable Color	Black

Contact Features

Ferrule Material	Brass
------------------	-------

Dimensions

Outside Cable Diameter	1.13 mm [.044 in]
Wire Size	32 AWG

Usage Conditions

Operating Temperature Range	-45 – 85 °C [-49 – 185 °F]
-----------------------------	----------------------------

Operation/Application

Operating Frequency Range	0 – 9 GHz
---------------------------	-----------

Other

Dielectric Material	FEP
Cable Assembly Length	.1 m [.328 ft]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.52% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1050525-1
2001 5003 02,SMA CABLE PLUG



TE Part # 1050524-1
2001 5003 00,SMA CABLE PLUG



TE Part # 2487514-1
WHIP ANT, SMA-STRAIGHT, 617-5000MHz



TE Part # 2108923-2
External Ant., SMA, Wi-Fi 6E(White)



TE Part # 2195632-1
EXTERNAL DUAL BAND GSM ANTENNA



TE Part # 2195891-1
Ext Antenna,SMA,active,GNSS,1558-1615MHz



TE Part # 2195889-1
Terminal Ant, 5G, SMA, 600-6000MHz



TE Part # 1052066-1
2037 5006 00,SMA RA CABLE PLUG



TE Part # 1050547-1
2001 5032 00



TE Part # 2195890-1
LTE Terminal Antenna











TE Part # 2487805-1
WHIP ANT, SMA-RIGHT ANGLE, 617-5000MHz













TE Part # 1053635-1
2081 0000 02



 <p>TE Part # 2108936-1 Terminal Antenna, SMA, WLAN Dual Band</p>	 <p>TE Part # 2108940-1 Terminal Ant, SMA, LTE,GNSS,698-2700MHz</p>	 <p>TE Part # 2334884-1 UMCC Micro-Coax receptacle, Gen 4</p>	 <p>TE Part # 2108936-2 Terminal Antenna, RP SMA, WLAN Dual Band</p>
 <p>TE Part # 2195889-2 External Ant, SMA, 600-6000MHz</p>	 <p>TE Part # 2108940-2 Terminal Ant,RP-SMA,LTE,GNSS,698-2700MHz</p>	 <p>TE Part # 2108923-1 External Ant., SMA, Wi-Fi 6E(Black)</p>	 <p>TE Part # 1052075-1 2037 5008 00,SMA RA CABLE PLUG</p>

Customers Also Bought

 <p>TE Part #MAF94300 Dipol,Hepta,SMAM 824-2500MHz,2-3dBi</p>	 <p>TE Part #801262-SF FN2070-36-08</p>	 <p>TE Part #31264 BUDG R 22-16 COMM 22-18 MIL 6</p>	 <p>TE Part #1-604772-0 CABLE TIE, 8" L, BLACK, 100PK</p>
 <p>TE Part #776231-1 35POS,PIN DIA 1.3,HDR ASSY, 180DEG,COD 1</p>	 <p>TE Part #1735284-2 SATA BACKPLANE RECEPTACLE, VERTICAL, SMT</p>	 <p>TE Part #3-1939755-6 .5FHR04H,220,S,GIG,30/Sn,HT,NS</p>	 <p>TE Part #2329497-2 SPRING FINGER 1.15H</p>
 <p>TE Part #928205-6 6P TELFIX BU-GEH</p>	 <p>TE Part #1311950-2 SCD,4710 5009 00,OSSP/BMMA</p>		

Documents



Product Drawings

[RF CA,UMCC4 TO SMA JACK,1.13MM,L100MM](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2016694-2_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2016694-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2016694-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

English