



Product Compliance

For compliance documentation, visit the product page on TE.com>







EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 1-2282291-5 2POS,HVA630,180 DEG,6 SQMM, PIGTAIL	 TE Part # 2141265-3 COVER,SEAL	 TE Part # 2141254-1 RADIAL SEAL 24 X 24	 TE Part # 9-2141264-2 SINGLE WIRE SEAL,AMP MCP6.3/4.8K
 TE Part # 2141264-4 SINGLE WIRE SEAL,AMP MCP6.3/4.8K	 TE Part # 2141264-3 SINGLE WIRE SEAL,AMP MCP6.3/4.8K	 TE Part # 2141630-1 5POS,HVA630,REC HSG ASSY, 180DEG,HVIL	 TE Part # 2141251-1 2POS,AMP MCP6.3/4.8K,REC HSG, SEALED
 TE Part # CAT-HVH5375 High-Voltage Header	 TE Part # 2141259-1 2POS, MIXED,REC HSG,ASSY	 TE Part # 2141265-4 COVER,SEAL	 TE Part # YHVA630-2PHI-HDR-A HVA630 2P (1-2141272-1) HEADER, KEY A
 TE Part # 2141252-1 CPA	 TE Part # 2141255-1 RETAINER	 TE Part # 2141262-3 SHIELDING,EMC	

Customers Also Bought

 TE Part #YHVA630-2PHM-6MM-A HVA630-2phm,6sqmm,Key A	 TE Part #YHVA630-2PHM-4MM-A HVA630-2phm,4sqmm,Key A	 TE Part #1587723-3 INNER FERRULE, SIZE C, HVA280	 TE Part #1587724-3 OUTER FERRULE, SIZE C, HVA280
--	---	---	---



Documents

Product Drawings

2POS,AMP MCP6.3/4.8K,REC HSG,ASSY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2141256-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2141256-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2141256-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English