

1-966096-1 ✓ ACTIVE

MQS

TE Internal #: 1-966096-1

18 Position, Black, Shield Assembly, PBTP

[View on TE.com >](#)



Automotive Parts > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: **18**

Primary Product Color: **Black**

Protection & Strain Relief Accessory Type: **Shield Assembly**

Primary Product Material: **PBTP**

Strain Relief: **Without**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Shield Assembly
---	-----------------

Configuration Features

Compatible With Connector Code	C – F
Number of Positions	18

Body Features

Primary Product Color	Black
Primary Product Material	PBTP

Mechanical Attachment

Strain Relief	Without
---------------	---------

Packaging Features

Packaging Method	Carton
Packaging Quantity	1000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 962108-2
2X9P MQS BU-GEH



TE Part # 2-929570-1
HEBEL F828864 MQS

Customers Also Bought



TE Part #5677562009
RNF-3000-3/1-0-STK



TE Part #2525596002
RBK-ILS-125-NR1-0-50MM



TE Part #165035
PLASTI-GRIP, RING, 12-10 1/4



TE Part #185875-1
26POS MQS REC



TE Part #185879-1
26W MQS COVER ASSY YELLOW




TE Part #1393315-2
V23132A2001A200=HCR



TE Part #1571983-4
GDH04S04=DIP SWITCH



TE Part #5-1625971-1
HSA25 47R 5%



TE Part #1670146-1
MCON 1.2 CB REC SWS SN



TE Part #8-2399606-2
1POS,HVP1400,ASSY,180DEG,COD B

Documents

Product Drawings

[MQS ABDECKKAPPE 18P](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-966096-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-966096-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-966096-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.