

HSHC4503R3J

✓ ACTIVE

CGS | CGS HS


TE Internal #: 2176735-7

3.3 ohm, Wire Wound, 5 %, Power Resistor, 450 W, 2 Terminations, ±50 ppm/°C, M6 Threaded Stud, Loose Piece - Tray, 41 mm [1.614 in] Height, CGS HS

[View on TE.com >](#)



Passive Components > Resistors > Chassis Mount Resistors > Power Resistors: Aluminium Housed, HSC



Resistor Type: **Power Resistor**
Resistance Class: **Up to 1kΩ**
Resistance Value: **3.3 Ω**
Power Rating: **450 W**
Element Type: **Wire Wound**

[All Power Resistors: Aluminium Housed, HSC \(485\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Resistance Class	Up to 1kΩ
Resistance Value	3.3 Ω
Power Rating	450 W
Passive Component Tolerance	5 %

Termination Features

Number of Terminations	2
Chassis Mount Resistor Termination Type	M6 Threaded Stud



Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes
--------------------------	----------------------------

Dimensions

Product Height	41 mm[1.614 in]
Product Length	234 mm[9.213 in]
Product Width	71.4 mm[2.811 in]

Usage Conditions

Temperature Coefficient	±50 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Loose Piece - Tray
------------------	--------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the



product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CAT-C339-H85913B
Power Resistors: Aluminium Housed,
HSC

Also in the Series | CGS HS




Automotive Housings(1)




Automotive Signal & Power Connector
Housings(1)



Chassis Mount Resistors(1069)



FFC Connectors(1)



High Speed Backplane Connectors(10)

Documents

Product Drawings
HSHC450 3R3 5%
English

CAD Files
Customer View Model
ENG_CVM_CVM_2176735-7_A.2d_dxf.zip
English
3D PDF
3D
Customer View Model

HSHC4503R3J

3.3 ohm, Wire Wound, 5 %, Power Resistor, 450 W, 2 Terminations, ±50 ppm/°C, M6 Threaded Stud, Loose Piece - Tray, 41 mm [1.614 in] Height, CGS HS



[ENG_CVM_CVM_2176735-7_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176735-7_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Aluminium Housed Power Resistors - Type HS Series

English