



Connectors > Connector Accessories > Heat Sinks



Device Type: SFP

Features

Product Type Features

Device Type	SFP
-------------	-----

Body Features

Primary Product Material	Stainless Steel
--------------------------	-----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2142970-5
CABLE ASSY, MICRO SFP+ TO STD SFP+, 4M



TE Part # 2142970-6
CABLE ASSY, MICRO SFP+ TO STD SFP+, 5M



TE Part # 2821033-8
QSFP TO [4]SFP+, 28G, 1M, 33AWG



TE Part # CAT-C11-H506
SFP+ to SFP+ I/O Cable Assembly: 26 AWG



TE Part # 1367646-4
Heatsink clip Stamped and Form



TE Part # 2110759-1
PT CONN ASSY 20 POS 16G SFP



TE Part # CAT-C11-H50626
SFP+ to SFP+ I/O Cable Assembly: 30 AWG



TE Part # 2142970-1
CABLE ASSY, MICRO SFP+ TO STD SFP+, 0.5M



TE Part # 2142970-7
CABLE ASSY, MICRO SFP+ TO STD SFP+, 6M



TE Part # 2142970-3
CABLE ASSY, MICRO SFP+ TO STD SFP+, 2M



TE Part # CAT-C11-H5062
SFP+ to SFP+ I/O Cable Assembly: 28 AWG




TE Part # 2142970-2
CABLE ASSY, MICRO SFP+ TO STD SFP+, 1M




TE Part # 2142970-4
CABLE ASSY, MICRO SFP+ TO STD SFP+, 3M


Customers Also Bought



TE Part #5-104362-2
03 MTE HDR SRST LATCH W/HLDWN



TE Part #2-1735482-4
0.8FH,R17H.5,100,30/Sn,TR,SC




TE Part #1-2170704-6
CAGE ASSY, QSFP28 1X1, SPRING, HS



TE Part #2170806-4
CAGE ASSEMBLY, 1X2, QSFP28,
SPRING, HS



TE Part #3-2198339-1
zSFP+ STACKED 2X6 RECEPTACLE
ASSEMBLY




TE Part #2-5406552-0
INV MJ,1X4,PNL GRD,LED (YG/YG)



TE Part #5767149-3
MICT,495,PLG,114,TAPE,CAP



TE Part #6123001-4
0.8FH,P08H.5,100,30/Sn,TR,SC



TE Part #2356580-4
SOCKET P4 TFLM KIT W/ COVER



TE Part #5-6450860-5
MBXLE VERT RCPT 1P+16S+1P

Documents

Product Drawings

[SFP+ ENHANCED 1X1 HEATSINK CLIP](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2057118-1_A_c-2057118-1-a.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2057118-1_A_c-2057118-1-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2057118-1_A_c-2057118-1-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English