H41K5DZA ✔ ACTIVE

Holsworthy | Holsworthy Holco

TE Internal #: 2-1879623-7

1.5K ohm, Thin Film, Precision Resistor, .5 %, .5 W, ±100 ppm/°C, Axial-Leaded, Copper Termination, 10 x 3.7 mm, Bandoliered, Holsworthy Holco

View on TE.com >

Passive Components > Resistors > Through-Hole Resistors







Resistor Type: **Precision Resistor**

Element Type: **Thin Film**

Power Rating: **.5 W**

Resistance Class: **1kΩ – 1MΩ**

Resistance Value: **1.5K Ω**

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film

Configuration Features

Number of Resistors	1

Electrical Characteristics

Operating Voltage	350 V
Power Rating	.5 W
Resistance Class	1kΩ – 1MΩ
Resistance Value	1.5K Ω
Passive Component Tolerance	.5 %

Body Features

Lead Type	Axial-Leaded

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	10 x 3.7 mm

Usage Conditions

Operating Temperature Range	-55 – 155 °C[-67 – 311 °F]
Temperature Coefficient	±100 ppm/°C

Packaging Features

Packaging Method	Bandoliered

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts

H41K5DZA


1.5K ohm, Thin Film, Precision Resistor, .5 %, .5 W, ±100 ppm/°C, Axial-Leaded, Copper Termination, 10 x 3.7 mm, Bandoliered, Holsworthy Holco




TE Part # 9-1879664-1
H8 10K 0.1% 15PPM




TE Part # 1879623-8
H4 1K3 0.1% 5PPM



TE Part # 2-1879622-2
H4P 1M0 1% 50PPM




TE Part # 5-1879642-1
H8 5K0 0.1% 25PPM




TE Part # 1879629-8
H4P 127R 0.5% 5PPM

Also in the Series | Holsworthy Holco




Through-Hole Resistors(6370)

Customers Also Bought



TE Part #EM7480-000
X2-1.5-0-SP-SM



TE Part #650916-5
048 EURO TYPE C PIN BL ASSY



TE Part #1-826942-6
16P MOD2 STIFT LEI



TE Part #6-1393227-5
RTE24006F




TE Part #6-1393254-7
W92-X112-1=M6/M7/M9/W6/W7



TE Part #2-1437661-9
TC6-03-PFH=COVER w/HOLES



TE Part #5-1614352-2
RN 0603 2K15 0.1% 10PPM CUT LENGTH



TE Part #1879623-7
H4 150K 0.1% 5PPM



TE Part #1-2007637-5
SFP+ assy 2x2 EMI Sprg 4 LP Sn Enhanced



TE Part #104071-1
10 SYSTEM 50 HDR SRST SHRD

Documents

Product Drawings

H4 1K5 0.5% 100PPM

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-1879623-7_BA1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1879623-7_BA1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2-1879623-7_BA1.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

Axial Leaded Precision Resistors - Type HOLCO Series

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English