



Connectors > Connector Accessories > Connector Adapters & Connector Savers



Connector Interface Adapter Type: **In-Series Adapter**

Body Orientation: **Straight**

Side A Interface: **N Type**

Side A Gender: **Jack**

Side B Interface: **N Type**

## Features

### Product Type Features

Connector Interface Adapter Type	In-Series Adapter
Side A Interface	N Type
Side A Gender	Jack
Side B Interface	N Type
Side B Gender	Jack
Connector System	Cable-to-Cable
Sealable	No

### Configuration Features

Number of Positions	1
---------------------	---

### Electrical Characteristics

Impedance	50 Ω
-----------	------

### Contact Features

RF Connector Center Contact Material	Beryllium Copper
RF Connector Center Contact Plating Material	Gold (Au)

### Mechanical Attachment



Connector Mounting Type	Board Mount
-------------------------	-------------

**Housing Features**

Body Orientation	Straight
------------------	----------

**Usage Conditions**

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC	Not Yet Reviewed
-----------------------------	------------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JAN 2025 (247)                  Candidate List Declared Against: JAN 2025 (247)                  SVHC &gt; Threshold:                  Pb (4% in Component Part)</p> <p><b>Article Safe Usage Statements:</b>                  Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
--	--

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---












Solder Process Capability	Not reviewed for solder process capability
---------------------------	--

Product Compliance Disclaimer









This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**



 <p>TE Part # 2016703-6 N M TO SMA M,18G,0.6M WITH ARMOR</p>	 <p>TE Part # 2016658-6 N M DOUBLE,18G,0.6M WITH ARMOR,PUR</p>	 <p>TE Part # 1-2016703-5 N M TO SMA M,18G,1.5M WITH ARMOR</p>	 <p>TE Part # 2016657-6 N M DOUBLE,18G,0.6M WITHOUT ARMOR</p>
 <p>TE Part # 1-2016703-0 N M TO SMA M,18G,1.0M WITH ARMOR</p>	 <p>TE Part # 1-2016658-0 N M DOUBLE,18G,1.0M WITH ARMOR,PUR</p>	 <p>TE Part # 2417718-1 N MALE TO N MALE FOR RF CABLE L600MM</p>	 <p>TE Part # 1-2016658-5 N M DOUBLE,18G,1.5M WITH ARMOR,PUR</p>
 <p>TE Part # 2081557-1 ADAPTOR N MALE TO 7-16 MALE</p>	 <p>TE Part # 1-2016657-0 N M DOUBLE,18G,1.0M WITHOUT ARMOR</p>	 <p>TE Part # 1-2016657-5 N M DOUBLE,18G,1.5M WITHOUT ARMOR</p>	

### Customers Also Bought

 <p>TE Part #ANT-GNCP-TH258L15 Antenna GNSS L1L5 25x25 1.13 UFL</p>	 <p>TE Part #F345203001 RAY-101-3.0(100)</p>	 <p>TE Part #1462041-3 IMB06CGR=IM RELAY 140mW 12V HDV</p>	 <p>TE Part #1462052-3 HF6 53 = 50OHM 140MW 5V MONO</p>
 <p>TE Part #1609133-3 6ESRM-3=F6920</p>	 <p>TE Part #1744423-1 EP 2.5 RCPT CONTACT, 24-20 AWG</p>	 <p>TE Part #6-1879337-8 CPF 0603 12K4 1% 50PPM 1K RL</p>	 <p>TE Part #1-1879339-1 CPF 0603 365K 1% 50PPM 1K RL</p>



## Documents

### Product Drawings

[ADAPTER N FEMALE TO N FEMALE 4-H FLG-MT](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2081563-1\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2081563-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2081563-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

[Product Specification](#)

English