

2203773-2 ✓ ACTIVE

MCON | MCON 1.2mm


TE Internal #: 2203773-2

4 Position Housing, Housing for Female Terminals, Wire-to-Wire, 4 mm [.16 in] Centerline, Sealable, Yellow, Wire & Cable, Power, MCON 1.2mm

[View on TE.com >](#)



Automotive Parts > Automotive Connectors > Automotive Housings



Connector & Housing Type: **Housing for Female Terminals**

Number of Positions: **4**

Sealable: **Yes**

Operating Temperature Range: **-40 – 150 °C [-40 – 302 °F]**

Number of Rows: **1**

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Primary Locking Feature	Clean Body
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1

Electrical Characteristics

Nominal Voltage Architecture	12 V
------------------------------	------

Body Features

Primary Product Color	Yellow
-----------------------	--------



Connector & Keying Code	B
-------------------------	---

Contact Features

Contact Size	1.2mm
Contact Type	Receptacle
Mating Tab Width	1.2 mm[.04 in]

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT
Centerline (Pitch)	4 mm[.16 in]

Dimensions

Product Width	26.5 mm[1.04 in]
Product Length	24.7 mm[.972 in]
Connector Height	19.5 mm[.768 in]

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
Operating Temperature (Max)	150 °C[302 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Other

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)

Candidate List Declared Against: JAN 2025 (247)

SVHC > Threshold:

Dodecamethylcyclhexasiloxane (D6) (.5% in Component Part)

Decamethylcyclopentasiloxane (D5) (.5% in 27520126664)

Octamethylcyclotetrasiloxane (D4) (.5% in Component Part)

Article Safe Usage Statements:

Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts


TE Part # 2203528-1
4P,1.2mm,CB,MCON,PeriSeal,30D,
HCR,RED

TE Part # 2303905-1
4POS,MCON 1.2,REC HSG,SLD,COD
NEUT




TE Part # 2272162-1
MCON WIRE DRESS, 4P, STRAIGHT

Also in the Series | **MCON 1.2mm**





Automotive Connector Caps & Covers
(15)

Automotive Housings(325)

Automotive Signal & Power Connector
Housings(321)

Automotive Terminals(90)

Customers Also Bought

TE Part #967056-1
MQS BLINDSTOPFEN4MMTE Part #967067-1
MQS SGL WIRE SEALTE Part #7-1452668-1
MCON 1.2 LL REC SWS SNTE Part #7-1452668-3
MCON 1.2 LL REC SWS AGTE Part #1-1718644-1
3POS, MCON 1.2 LL REC SEALEDTE Part #1-1718646-1
6POS, MCON 1.2 LL REC SEALED

Documents

Product Drawings

4POS, MCON 1.2 CB REC 1p TL SEALED

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2203773-2_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2203773-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2203773-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Instruction Sheets

Instruction Sheet (U.S.)

English