



Connectors > Connector Accessories > Connector Adapters & Connector Savers



Connector Interface Adapter Type: **Connector Saver**

Body Orientation: **Straight**

Number of Positions: **15**

Centerline (Pitch): **2.29 mm [.09 in]**

Contact Current Rating (Max): **5 A**

Features

Product Type Features

Connector Interface Adapter Type	Connector Saver
----------------------------------	-----------------

Configuration Features

Number of Positions	15
---------------------	----

Body Features

Body Plating Material	Gold
Body Material	Brass

Contact Features

Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Beryllium Copper
Contact Size	Size 22
Contact Current Rating (Max)	5 A

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Body Orientation	Straight
Centerline (Pitch)	2.29 mm[.09 in]

Usage Conditions

Operating Temperature Range	-67 – 257 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application



Compatible With Connector Shell Size	1
Circuit Application	Signal

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (4% in Contact/Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






Customers Also Bought



TE Part #803143-000
55A6262-24-9/96-9CS2275




TE Part #355829-000
22759/34-22-5



TE Part #58628-1
PROCrimp T&D 26-14 ULTRAFast



TE Part #211012-4
AMPLIMITE Conn SVR,44 POS,TRW



TE Part #2-520080-2
ULTRA-FAST .110/.125 ASY REC 22-18
TPBR



TE Part #787004-3
.8MM SCREWLOCK BRDMT,BULK



TE Part #2-2176308-7
RP 1E 0.1W 249K 0.1% 25PPM 5K RL



TE Part #6609105-2
PS0SXSXB0=C1093



TE Part #50334-3
SOLIS,RING,26-22,2,UNPLTD

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_211010-4_AU.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_211010-4_AU.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_211010-4_AU.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.