



Connectors > D-Shaped Connectors



Number of Positions: 15
Connector & Housing Type: Receptacle
Connector System: Cable-to-Cable
Connector Mounting Type: Panel Mount
Connector Shell Size: 2

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Cable-to-Cable
Connector Shell Size	2
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	15
Power/Signal/Coax Combination	No

Body Features

Mating Retention Feature Material	Copper Alloy
D-Sub Connector Insert Arrangement	MS18274-1

Contact Features

	50 µin
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy
Contact Type	Socket
Contact Size	Size 20
Contact Current Rating (Max)	7.5 A



Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mounting Hole Diameter	3.05 mm[.12 in]
Connector Mounting Type	Panel Mount
Mating Alignment	Without

Housing Features

Centerline (Pitch)	2.77 mm[.109 in]
--------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides




on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 91067-2
INSERTION/EXTRACTION TOOL



TE Part # 206793-1
SZ 20,SOCKET, NON-MAG

Customers Also Bought



TE Part #ZPF000000000206121
DBAS 979G 17-35 PN



TE Part #ZPF000000000206954
DBAS 974-17-35 SN



TE Part #ZPF00000000003598
724-0003-20




TE Part #211633-4
HD109 9 POS GMT ASY RCPT




TE Part #211636-4
HD109 37 POS GMT ASY RCPT




TE Part #211640-4
GMT ASY,PLUG,25 POS,AMPLIMITE




TE Part #211641-4
HD 109 37 POS GMT ASY PLG HSG



TE Part #211642-4
HD109 50 POS GMT ASY PLUG



TE Part #1-2157481-2
AMPLIMITE IP67, SZ2, 109, 15 POS, RCPT



TE Part #EG6941-000
55PC021A-26-9

Documents

- CAD Files
- 3D PDF
- 3D



Customer View Model

[ENG_CVM_CVM_211634-4_AA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_211634-4_AA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_211634-4_AA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.