

2321561-2 ✓ ACTIVE


TE Internal #: 2321561-2

Power Cable Assemblies, Double-Ended, .23in [6mm] Diameter,
Length 1.34 ft [.41 m], Black / Red, -40 – 150 °C [-40 – 302 °F],
Power, Black Housing

[View on TE.com >](#)



Cable Assemblies > Copper Cable Assemblies > Power Cable Assemblies



Power Cable Assembly Configuration: **Double-Ended**

Power Cable Assembly Overall Outside Cable Diameter: **6 mm [.23 in]**

Power Cable Assembly Shielded: **No**

Cable Assembly Length: **.41 m [1.34 ft]**

Power Cable Assembly Color: **Black, Red**

Features

Product Type Features

Power Cable Assembly Shielded	No
Power Cable Assembly Type	Power

Configuration Features

Power Cable Assembly Configuration	Double-Ended
------------------------------------	--------------

Body Features

Power Cable Assembly Color	Black, Red
----------------------------	------------

Housing Features

Power Cable Assembly Housing Color	Black
------------------------------------	-------

Dimensions

Power Cable Assembly Overall Outside Cable Diameter	6 mm [.23 in]
Wire Size	36 CMA

Usage Conditions

Operating Temperature Range	-40 – 150 °C [-40 – 302 °F]
-----------------------------	-----------------------------

Other



Cable Assembly Length	.41 m[1.34 ft]
-----------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2322470-1
CA, PRESS-FIT, HF

TE Part # 2322044-5
MBXL R/A HDR STR 2ACP + 12S + 2ACP HF

Customers Also Bought



TE Part #3-5353652-6
5FHP08H,440,B,GIG,08/Sn,HT,NSYes



TE Part #2-1926730-5
AssyMINIPAKHDL25a10pRAplugBdlk



TE Part #2-1926739-5
AssyMinipak Hdl25s10pRARectptSc



TE Part #1643903-1
CC - CROWN CLIP Senior II 538-0068-00100



TE Part #2289129-2
ZQSFP+ CAGE& CONN 2X2, EMI SPRING, 4 LP




TE Part #1643903-3
CC - CROWN CLIP Senior II, AG PLATING




TE Part #2324193-2
CAGE ASSY, QSFP-DD 1X1, STANDARD



TE Part #2187793-1
SW PIR RECT, 100OHM, 4X10



TE Part #2187794-1
SW PIR RECT, 85OHM, 8X10



TE Part #2314316-1
CA, OCP, HALOGEN FREE

Documents

Product Drawings

[CA, YOSEMITE2](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2321561-2_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2321561-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2321561-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English

Product Environmental Compliance

TE Material Declaration

English