



TE Internal #: 2326768-2
 4 Position, Receptacle, Connector Kit, Crimp, Wire-to-Motor, Gold (Au), Normal, UL 94V-0, 4.6 mm [.181 in] Centerline, 2 Row, 370 VAC, Sealable
[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Kit**
 Connector & Housing Type: **Receptacle**
 Mating Retention: **With**
 Mating Retention Type: **Screwlocks**
 Termination Method to Wire & Cable: **Crimp**

Features

Product Type Features

Connector Product Type	Connector Kit
Connector & Housing Type	Receptacle
Connector System	Wire-to-Motor
Insertion Force Type	Normal
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Loaded Positions	4
Number of Positions	4
Number of Rows	2

Electrical Characteristics

Operating Voltage	370 VAC
-------------------	---------

Body Features

Seal Type	Panel Gasket
-----------	--------------



Contact Features

Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Gold (Au)
Contact Retention Within Housing	With
Contact Current Rating (Max)	7 A
Wire Contact Termination Area Plating Material	Nickel

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mating Retention	With
Mating Retention Type	Screwlocks
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	4.6 mm [.181 in]
--------------------	------------------

Dimensions

Row-to-Row Spacing	4.6 mm [.181 in]
--------------------	------------------

Usage Conditions

Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Shielded	No
Circuit Application	Power

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247)



Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2261091-6
RECEPTACLE CONTACT 4POS.,MMC-PUSH ON-P-F

TE Part # 2255334-1
SDE12 HAND TOOL FOR MMC PUSH ON P-F REC.

Customers Also Bought



TE Part #66740-8
TYPE XII FEMALE CONT (L.P.)



TE Part #175363-2
DYNAMIC D-3500 REC HSG 4P



TE Part #178289-6
DYNAMIC 3100 REC HSG 12P DBL



TE Part #CAT-D9934-A83
Contact: Component To Wire ; 20-45A * 20-8 wire size



TE Part #3-917807-2
DYNAMIC D-5200M REC HSG 4P X-Y



TE Part #1-1318120-3
DYNAMIC D-2100 REC HSG 3P



TE Part #1827587-2
DYNAMIC D1000 REC CONT M AU 0.38um L/P



TE Part #1-1827864-0
DYNAMIC 1200D REC HSG 20P X BLACK



Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2326768-2_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2326768-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2326768-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English